



RoHS Compliant

| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|---|---|---|---|---|
| B | | NEW | | |





RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm




| | A | B | C | D |
|---|---|---|---|---|
| DIM A | 8.8 | 9.3 | 10.0 | 10.5 |

NOTES:
SPECIFICATION:
1. CURRENT RATING: 5.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: −30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

| A1 | GND | B12 | GND |
|---|---|---|---|
| A4 | VBUS | B9 | VBUS |
| A5 | CC1 | B8 | SBU2 |
| A6 | DP1 | B7 | DN2 |
| A7 | DN1 | B6 | DP2 |
| A8 | SBU1 | B5 | CC2 |
| A9 | VBUS | B4 | VBUS |
| A12 | GND | B1 | GND |
| PIN | SIGNAL NAME | PIN | SIGNAL NAME |

| NO. | DESCRIPTION | MATERIAL | REMARKS | QTY |
|---|---|---|---|---|
| 6 | SHELL | STAINLESS STEEL | NI/SN Plated | 1PCS |
| 5 | SHIELDING PLATE | STAINLESS STEEL | --- | 1PCS |
| 4 | MD | HIGH TEMPERATURE PLASTIC | BLACK | 1PCS |
| 3 | CONTACT | COPPER ALLOY | Au/NI Plated | 1SET |
| 2 | CONTACT | COPPER ALLOY | Au/NI Plated | 1SET |
| 1 | HOUSING | HIGH TEMPERATURE PLASTIC | BLACK | 1PCS |


| | | | |
|---|---|---|---|
| X. ±0.50 | X.° ± 2° | UNITS mm | 广东创粤科技有限公司 |
| .X ±0.30 | .X° ± 1° | MAT'L | TITLE: TYPE-C 16PIN 立贴母座 H=10.0MM |
| .XX ±0.10 | .XX° ± 0.5° | | |
| .XXX ± 0.05 | | FINISH | TYPE-C-16P-H10.0SMT-08605 DWG NO.: |
| | | Q'TY | CHKD: |
| | | | DR: |

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

| SCALE | SHEET | REV. |
|---|---|---|
| 1/1 | 1/1 | A1 |

| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|---|---|---|---|---|
| B | | NEW | | |


RoHS Compliant





① 产品入载带示意图





② 卷盘贴标签示意图



③ 10盘产品叠层示意图




④ 产品入外箱示意图




⑤ 外箱封箱示意图

NOTE:

1.QUANTITY/REEL:450 PCS
数量/卷:450 PCS
QUANTITY/INNER CARTON:450 X 10 = 4500 PCS
数量/箱: 450 X 10 = 4500 PCS

2.FREE 16 CAVE IN THE FRONT CARRIER ADN FREE 16 CAVE IN THE END CARRIER.
包装带内圈空16格,外圈空16格.

| ITEM | DESC. | MATERIAL | REMARKS | QTY |
|---|---|---|---|---|
| 1 | 成品 | | C TYPE母座成品 | 4500 |
| 2 | CARRIER TAPE | PET | W=24mm T=0.50mm | 7.7M |
| 3 | COVER TAPE | PET | W=13.3mm T=0.05mm | 7.7M |
| 4 | 小标签 | | L102mm*W59mm | 10 |
| 5 | 卷盘 | PS | ø380mm*H28.4mm | 10 |
| 7 | 外标签 | | L102mm*W102mm | 1 |
| 9 | 外箱 | A=A | L395mm*W395mm*H300mm | 1 |

| | | | |
|---|---|---|---|
| X. ±0.50 | X.° ± 2° | UNITS mm | 广东创粤科技有限公司 |
| .X ±0.30 | .X° ± 1° | MAT'L | TITLE: TYPE-C 16PIN 立贴母座 H=10.0MM |
| .XX ±0.10 | .XX° ± 0.5° | | |
| .XXX ± 0.05 | | FINISH | TYPE-C-16P-H10.0SMT-08605 DWG NO.: |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD | | Q'TY | CHKD: |
| | | | DR: |

| SCALE | SHEET | REV. |
|---|---|---|
| 1/1 | 1/1 | A1 |