
RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.04.24




SPECIFICATIONS
1. Current rating: 7A
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 1000MΩ Min.
4. Withstanding voltage: 1500V AC/ minute.
5. Contact resistance: 20mΩ Max.


Material:
Insulator Material:PA66 UL94V-0
Contact Material:Brass
Contact Plating:Tin-Plated
Mate with XFCN P3960 series Housing

Ordering Code:

M3960R-03N2P
1 2

1.序列号
2.Pin位数: 03P





P.C.B LAYOUT

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: M3960R-03N2P

TITLE: 3.96mm Crimp Style Connectors

XFCN兴飞连接器
0769-82001899
www.xfconn.com
DWG NO:

APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2024.04.24	NONE	1/1	A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN