



ROHS Compliant


MAPX	MODIFICATION	DATE	DRAW	APPROVE















RECOMMENDED P.C.B. LAYOUT (T:0.80mm)

TOLERANCE UNSPECIFIED ±0.05mm



NOTES:


1. Material & Finish:See the list;
2. Mechanical:
   - 2.1.Mating force:5−20Nf;
   - 2.2.Unmating force:Initial:8−20Nf;Final:6−20Nf;
   - 2.3.Durability:10000 Cycles;
3. Electrical:
   - 3.1.Current Rating:
     VBus Pins:5A, Vconn Pin:1.25A, Other Pins:0.25A;
   - 3.2.Voltage Rating:20V Max;
   - 3.3.Withstanding volage:100V AC R.M.S;
   - 3.4.Contact resistance:40mΩ Max.;
   - 3.5.Insulation Resistance:100MΩ Min.;
4. Environmental:
   - 4.1.Operating temperature:−35°C~+85°C;
   - 4.2.Salt Spray Test:48H Min.(No oxidation or rust);
   - 4.3.Wetting Temperature:265±5°C,5±0.5s


NO.	PART NAME	Q'TY	MATERIAL	FINISH
5	Shell	1	STAINLESS STEEL, T=0.30mm	50u"Ni Min.
4	Middle Clip	1	STAINLESS STEEL, T=0.15mm	No Plating
3	Down Contact	8	COPPER ALLOY, T=0.15mm	Mating area: Au G/F&3u"&15u"&30u"Min, Solder Tails: Sn 100u"Min, Underplate: 50u"Min Ni overall
2	Top Contact	8	COPPER ALLOY, T=0.15mm	
1	Housing	1	HIGH TEMPERATURE PLASTIC,UL 94 V-0	Black


MANUFACTURE DWG	东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co,Ltd		
UNLESS OTHERWISE SPECIFED TOLERANCES		TITLE:Type−C Receptacle 16P heighten 1.9H SMT L8.0	
		PAR	TYPE−C−637−WSCD19
		DWN	Lucas
		CHKD	Ethan
		APVD	Jacob
DECIMALS: / ANGLES:		SCALE1:1	UNIT:MM
X.:±0.50 / X.°:±5°			
X.X:±0.35 / X.X°:±3°			
X.XX:±0.25 / X.XX°:±2.5°	CUSTOMER COPY	SIZE:A4	SHEET:1F2 REV:A

ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE







说明:

1.每卷前后各空12PCS,尾部用美纹胶纸封住;
2.将产品放满盘后,再卷一圈保护带,用美纹胶纸
将其封住,并贴上1Pcs物料标签;
3.每10卷盘一叠共9000Pcs装入1个外箱内;
4.在搬运过程中要轻拿轻放;
5.在运输中不可堆放过多(1.8M最高),不可重压;
6.跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a.产品不可跑出下带凹槽;
b.产品不可有摔伤,变形;
c.内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
⓪	TYPE C 16P加高1.9mm母座成品		
①	载带	W=24mm,T=0.40mm	900PCS/盘
②	盖带	W=21.3mm	
③	卷盘	ø380*100*24.4mm	10PCS/箱
④	ROHS标签		10PCS/箱
⑤	产品标签		10PCS/箱
⑥	纸箱	390*390*310mm	9000PCS/箱

MANUFACTURE DWG	东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co,Ltd		
UNLESS OTHERWISE SPECIFED TOLERANCES	TITLE:Type-C Receptacle 16P heighten 1.9H SMT L8.0		
	PAR	TYPE-C-637-WSCD19	
	DWN	Lucas	
	CHKD	Ethan	
	APVD	Jacob	
DECIMALS: X.:±0.50 X.X:±0.35 X.XX:±0.25 / ANGLES: X.°:±5° X.X°:±3° X.XX°:±2.5°	SCALE1:1	UNIT:MM	
CUSTOMER COPY	SIZE:A4	SHEET:1F2	REV:A