




www.dzyjzj.com Tel:0755-27575531 Fax:0755-27576267













PCB LAYOUT THICKNESS 1.60mm

TOLERANCE:+/-0.05mm





NOTES:

1. MATERIAL:
   HOUSING:THERMOPLASTIC,UL 94V-0,BLACK;
   CONTACT:COPPER ALLOY
2. FINSH:
   CONTACT:Ni 1.3~3um,Sn 2~6um
   SPECIFICATIONS:
   VOLTAGE RATING: AC/DC 250V
   CURRENT RATING: 2A PER PIN
   INSULATION RESISTANCE: 1GOHM MIN
   CONTACT RESISTANCE: 30mΩ Max.
   OPERATION TEMPERATURE:-40° TO +85°
3. ⊛ IS FAI SIZE
4. C IS FIRST INSPECTION SIZE
5. CTQ IS INSPECTION SIZE.
6. CPK IS CPK SIZE

ITEM	NAME	Q'TY	MATERIAL	PLATING OR CLOCR
1	HOLD DOWN	2	BRASS T=0.30mm	Ni 1.3~3um Sn 2~6um
2	CONTACT	4	BRASS T=0.30mm	Ni 1.3~3um Sn 2~6um
3	HOUSING	1	LCP,UL94V-0	BLACK CLOCK

深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.° ±2° X.X' ±0.5'	DRAWED BY : 陈一鸣	DATE : 2014-02-23	PART NAME: BTW 4P 5.45H CONNECTOR
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW01-BTW04-545B
UNIT: mm [inch]	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO. / DRAW NO: HYC-2609231437
SCALE:1:1 SIZE: A4			SHEET NO. 1 OF 1