



RoHS


REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25























适用扁平线(Applicable Flat Cable)

Ordering Code:

F0501-B-xx-20T-R
1 2 3 4

1.序列号
2.Pin位数:04=04
3.电镀方式:T=镀锡
4.包装方式:R=卷装

技术指标：
1.塑件表面应光洁、无毛边、无明显收缩、 缺陷、裂纹等现象.
2.温度范围(Temperature range)：-25℃～+85℃
3.额定电流(Current rating):0.5A AC/DC
4.额定电压(Rated voltage)：50V AC/DC
5.接触电阻(Contact resistance)：≤0.03 Ω.
6.绝缘电阻(Insulation resistance):≥500M Ω.DC500V.

CKT	DIMA	DIMB	DIMC	DIMD	CKT	DIMA	DIMB	DIMC	DIMD
04	1.5	2.56	7.60	5.20	33	16.00	17.06	22.10	5.20
05	2.0	3.06	8.10		34	16.50	17.56	22.60	
06	2.5	3.56	8.60		35	17.00	18.06	23.10	5.75
07	3.0	4.06	9.10		36	17.50	18.56	23.60	
08	3.5	4.56	9.60		37	18.00	19.06	24.10	
09	4.0	5.06	10.10		38	18.50	19.56	24.60	
10	4.5	5.56	10.60		39	19.00	20.06	25.10	
11	5.0	6.06	11.10		40	19.50	20.56	25.60	
12	5.5	6.56	11.60		41	20.00	21.06	26.10	
13	6.0	7.06	12.10		42	20.50	21.56	26.60	
14	6.5	7.56	12.60		43	21.00	22.06	27.10	
15	7.0	8.06	13.10		44	21.50	22.56	27.60	
16	7.5	8.56	13.60		45	22.00	23.06	28.10	
17	8.0	9.06	14.10		46	22.50	23.56	28.60	
18	8.5	9.56	14.60		47	23.00	24.06	29.10	
19	9.0	10.06	15.10		48	23.50	24.56	29.60	
20	9.5	10.56	15.60		49	24.00	25.06	30.10	
21	10.00	11.06	16.10		50	24.50	25.56	30.60	
22	10.50	11.56	16.60		51	25.00	26.06	31.10	
23	11.00	12.06	17.10		52	25.50	26.56	31.60	
24	11.50	12.56	17.60		53	26.00	27.06	32.10	
25	12.00	13.06	18.10		54	26.50	27.56	32.60	
26	12.50	13.56	18.60		55	27.00	28.06	33.10	
27	13.00	14.06	19.10		56	27.50	28.56	33.60	
28	13.50	14.56	19.60		57	28.00	29.06	34.10	
29	14.00	15.06	20.10		58	28.50	29.56	34.60	
30	14.50	15.56	20.60		59	29.00	30.06	35.10	
31	15.00	16.06	21.10		60	29.50	30.56	35.60	
32	15.50	16.56	21.60						

序号	名称	材质
④	焊片	铜合金/表面镀锡
③	后盖	LCP UL94V-0 黑色
②	端子	铜合金/表面镀锡
①	基座	LCP UL94V-0 本色

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: F0501-B-xx-20T-R

TITLE: FPC0.5mmPitch 拉拔卧式下接(H=2.0)

DWG NO: /

APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2024.05.27	NONE	1/1	A1

XFCN兴飞连接器
0769-82001899
www.xfconn.com