


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		







RECOMMENDED P.C.B. LAYOUT (俯视图)
TOLERANCE UNSPECIFIED ±0.05mm








AFTER MATING





SPECIFICATION:

1、ELECTRICAL:
1.1 CURRENT RATING:5A;
1.2 CONTACT RESISTANCE:40mΩ Max;
1.3 DIELECTRIC WITHSTANDING VOLTAGE:100V AC;
1.4 INSULATION RESISTANCE:100 MΩ MIN;

2、MECHANICAL;
2.1 MATING FORCE:5~20N;
2.2 UNMATING FORCE:8~20N;
2.3 DURABILITY:10000 CYCLES;6~20N AFTER DURABILITY TEST;

3、MATERIAL:
3.1 HOUSING&MOLDING:BLACK LCP UL94V-0;
3.2 TERMINAL:C7025 T=0.15mm;
3.3 SHELL:SUS304 T=0.30mm;
3.4 MID PLATE:SUS304 T=0.15mm;

4、PLATING SPECIFICATION:
4.1 TERMINAL:CONTACT POINT GOLD PLATED 3u "Min
PIN WELDING AREA GOLD PLATED 1u" Min.
4.2 NI 40U" Min. UNDER PLATED OVER ALL.
4.2 SHELL:PLATED Ni 50u" MIN(Salt spray 48H)

5、ELECTROPLATED PRODUCTS NEED TO UNDERGO TIN ADHESION TESTING: THE TIN ADHESION AREA SHOULD REACH OVER 95%.

6、SMT REFLOW SOLDERING (PEAK VALUE 260 °C ± 5 ° C) SHALL BE FREE OF BLISTERING, GLUE MELTING AND POOR COLOR CHANGE (DEFORMATION WITHIN TOLERANCE)

7、OPERATING TEMPERATURE: -40°C~+85°C

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	Dn2
A7	D-	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

X. ±0.50	X.° ± 2°	UNITS	mm
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	
.XXX ± 0.05			

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE:
TYPE-C 16P母座 立插 针长1.80 H=24.50 A款

APPD:

CHKD:


DR:

DWG NO.:
TYPE-C-16P-H24.50-150154


SCALE	SHEET	REV.
1/1	1/1	A1

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




① PE真空盒(1Set).




② 90PCS/盒




③ 50盒/箱(4.5K).



④ 每箱竖放25盒*2,若尾数箱在空间处加装填充物.



⑤ 外箱用透明胶纸带封"工"字型.



⑥ 依图示粘贴产品或RoHS标签.

序号	物料名称	物料编号	规 格	描 述
04	纸箱	B-05-0004	430mm*330mm*180mm	1 PCS
03	上盖	B-01-0016	PET透明 T0.3*L305*W205*H11mm	50 PCS
02	下盒	B-01-0015	PET透明 T0.3*L305*W205*H11mm	50 PCS
01	连接器	JSX-TC16FA-0200	16PIN, DIP	4500 PCS

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.10	.XX° ± 0.5°	MAT'L
.XXX ± 0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE: TYPE-C 16P母座 立插 针长1.80 H=24.50 A款

APPD:

CHKD:

DR:

DWG NO.: TYPE-C-16P-H24.50-150154

SCALE	SHEET	REV.
1/1	1/1	A1