

RoHS


REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.11.17




SPECIFICATIONS
1. Current rating: 7A
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 1000MΩ Min.
4. Withstanding voltage: 800V AC/ minute.
5. Contact resistance: 20mΩ Max.

Material:
Insulator Material:PA66 UL94V-0 (2)
Contact Material:Brass
Contact Plating:Tin-Plated
Mate with XFCN P3960 series Housing







X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: M3960V-05N3

TITLE: 3.96mm Crimp Style Connectors

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2025.11.17	NONE	1/1	A1

XFCN兴飞连接器
0769-82001899
www.xfconn.com

DWG NO: /