



版次(Edition)	变更摘要(Change The Content)	日期(Date)
0	新产品发行(The first edition)	2022.3.12
1	料号更新(Material number update)	2024/12/10

序号 (NO.)	品名 (TITLE)	材质 (Material)
①	0.5掀盖立式胶芯(H=5.4) 0.5 easy-on S/T Housing(H=5.4)	LCP UL94V-0 本色 Natural
②	0.5掀盖立式后盖(H=5.4) 0.5 easy-on S/T Actuator(H=5.4)	LCP UL94V-0 黑色 Black
③	0.5掀盖立式端子(H=5.4) 0.5 easy-on S/T Terminal(H=5.4)	铜合金/表面镀金 Copper Alloy/Gold Plating
④	0.5掀盖立式焊片(H=5.4) 0.5 easy-on S/T Solder tab(H=5.4)	铜合金/表面镀锡 Copper Alloy/Tin Plating












≤50Pin
≥50Pin



适用扁平线(Applicable Flat Cable)





适用线路板(PCB LAYOUT)

技术指标(Technical Index):

1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)

2.温度范围(Temperature range):-25° C～85° C.

3.额定电流(Rated Current):0.5A.

4.额定电压(Rated voltage):50V AC/DC.

5.接触电阻(Contact resistance):≤50mΩ.

6.绝缘电阻(Insulation resistance):≥500MΩ.

7.耐电压(Withstanding Voltage):150V AC/1Minute

8.产品料号(Product material No.):

XL0554013—** * *—***

NO OF CKT(产品PIN数)

Plating(电镀方式)
0:端子全雾锡(Terminal all fog tin)
1:端子全镀金(Terminal G/F OVER ALL)
2:端子点镀金(Contact and weld area gold-plated)

流水码
(Serial number)

Packing(包装方式)
R:REEL(卷装)

RoHS

一般公差(TOLERANCE)
X. ±.50 .XX ±.10
.X ±.20 .XXX ±.05
ANGLES ±1°

ZGWD 浙江温达电子有限公司
ZHEJIANG WENDA ELECTRONICS CO.,LTD

品名 (TITLE)
0.5 Pitch掀盖立式正脚(H=5.4)
0.5 Pitch easy-on S/T Normal Pin(H=5.4)

料号 (DWG.NO)
XL0554013-****-***

制图 (DR) Anlan
校对 (CHKD) 田峰
审核 (APPD) 黄志明

比例 (SCALE) 1:1
单位 (UNITS) mm
张数 (SHEET) 1 OF 2
SIZE A4
REV A

CKT	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
5	2.00	3.06	6.00	4.40	2.50	4.00
6	2.50	3.56	6.50	4.90	3.00	4.50
7	3.00	4.06	7.00	5.40	3.00	5.00
8	3.50	4.56	7.50	5.90	4.00	5.50
9	4.00	5.06	8.00	6.40	4.00	6.00
10	4.50	5.56	8.50	6.90	4.00	6.50
11	5.00	6.06	9.00	7.40	4.00	7.00
12	5.50	6.56	9.50	7.90	4.00	7.50
13	6.00	7.06	10.00	8.40	4.00	8.00
14	6.50	7.56	10.50	8.90	4.00	8.50
15	7.00	8.06	11.00	9.40	4.00	9.00
16	7.50	8.56	11.50	9.90	4.00	9.50
17	8.00	9.06	12.00	10.40	4.00	10.00
18	8.50	9.56	12.50	10.90	4.00	10.50
19	9.00	10.06	13.00	11.40	4.00	11.00
20	9.50	10.56	13.50	11.90	4.00	11.50
21	10.00	11.06	14.00	12.40	4.00	12.00
22	10.50	11.56	14.50	12.90	4.00	12.50
23	11.00	12.06	15.00	13.40	4.00	13.00
24	11.50	12.56	15.50	13.90	8.00	13.50
25	12.00	13.06	16.00	14.40	8.00	14.00
26	12.50	13.56	16.50	14.90	8.00	14.50
27	13.00	14.06	17.00	15.40	8.00	15.00
28	13.50	14.56	17.50	15.90	8.00	15.50
29	14.00	15.06	18.00	16.40	8.00	16.00
30	14.50	15.56	18.50	16.90	8.00	16.50
31	15.00	16.06	19.00	17.40	8.00	17.00
32	15.50	16.56	19.50	17.90	8.00	17.50

CKT	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
33	16.00	17.06	20.00	18.40	8.00	18.00
34	16.50	17.56	20.50	18.90	8.00	18.50
35	17.00	18.06	21.00	19.40	8.00	19.00
36	17.50	18.56	21.50	19.90	8.00	19.50
37	18.00	19.06	22.00	20.40	8.00	20.00
38	18.50	19.56	22.50	20.90	8.00	20.50
39	19.00	20.06	23.00	21.40	8.00	21.00
40	19.50	20.56	23.50	21.90	8.00	21.50
41	20.00	21.06	24.00	22.40	8.00	22.00
42	20.50	21.56	24.50	22.90	8.00	22.50
43	21.00	22.06	25.00	23.40	8.00	23.00
44	21.50	22.56	25.50	23.90	8.00	23.50
45	22.00	23.06	26.00	24.40	8.00	24.00
46	22.50	23.56	26.50	24.90	8.00	24.50
47	23.00	24.06	27.00	25.40	8.00	25.00
48	23.50	24.56	27.50	25.90	8.00	25.50
49	24.00	25.06	28.00	26.40	8.00	26.00
50	24.50	25.56	28.50	26.90	8.00	26.50
51	25.00	26.06	29.00	27.40	8.00	27.00
52	25.50	26.56	29.50	27.90	8.00	27.50
53	26.00	27.06	30.00	28.40	8.00	28.00
54	26.50	27.56	30.50	28.90	8.00	28.50
55	27.00	28.06	31.00	29.40	8.00	29.00
56	27.50	28.56	31.50	29.90	8.00	29.50
57	28.00	29.06	32.00	30.40	8.00	30.00
58	28.50	29.56	32.50	30.90	8.00	30.50
59	29.00	30.06	33.00	31.40	8.00	31.00
60	29.50	30.56	33.50	31.90	8.00	31.50

RoHS

一般公差(TOLERANCE)
X. ±.50 .XX ±.10
.X ±.20 .XXX ±.05
ANGLES ±1°

ZGWD 浙江温达电子有限公司
ZHEJIANG WENDA ELECTRONICS CO.,LTD

品名 (TITLE)
0.5 Pitch掀盖立式正脚(H=5.4)
0.5 Pitch easy-on S/T Normal Pin(H=5.4)

料号 (DWG.NO)
XL0554013-****-***

制图 (DR) Anlan
校对 (CHKD) 田峰
审核 (APPD) 黄志明

比例 (SCALE) 1:1
单位 (UNITS) mm
张数 (SHEET) 2 OF 2
SIZE A4
REV A