


CUSTOMER DRAWING


REV. 版本	ECN NO. ECN编号	DATE 日期	DESCRIPTION 内容描述	APPROVED BY 核准
A0	——	2026/09/14	NEW RELEASE	APLIN







CIRCUIT










P.C.B LAYOUT



ITEM	PART NAME	MATERIAL
8	LUCENCY FLAKE	PET
7	FIXITY	PC
6	COVER	ABS
5	TERMINAL	Bronze Silver Plated
4	CONTACT	SUS
3	LED	GaAsP/GaP
2	BUTTON	PA66/POM
1	HOUSING	PA66

NOTES:
1.RATING: 12VDC 50mA
2.CONTACT RESISTANCE: 100mΩ Max
3.INSULATION RESISTANCE: 100MΩ 250VDC FOR 1MIN
4.DIELECTRIC STRENGTH: 250VAC(50/60Hz) FOR1MIN
5.LIFE TEST:100,000 CYCLES
6.OPERATION FORCE&TRAVEL: SEE SPECIFICATION

佛山市皓通电子有限公司
FoShan Haoswitch Electronic Co.,Ltd.

DRAWN BY 制 图	YUAN	2026/09/14	SCALE 比 例	FREE	PRODUCT NAME 产品名称	tact SWITCH
CHECKED BY 核 对	APLIN	2026/09/14	PAGE 页 面	1/1	DESCRIPTION 产品描述	
APPROVED BY 批 准	ZHANG	2026/09/14	UNIT 单 位	mm		
TOLERANCE 未标注公差	X: ±0.5 .X: ±0.3 .XX: ±0.2	X°: ±5° .X°: ±2°	PROJECTED 投影		PART NO. 物料编号	H26-PB01-142L-W-G5
					SIZE 尺寸 A4	DRAWN NO. 图纸编号 HTDW20260914023

https://www.howswitch.com