

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		







RECOMMENDED PCB LAYOUT(TOP VIEW)
DEFAULT TOLERANCE:±0.05

1. 材料
   A. 主体：LCP，黑色/白色，UL 94-V0;
   B. 端子：高导铜C7025，电镀刷金;
   C. 外壳：不锈钢304，镀全镍;
   D. 卡钩：不锈钢304;
2. 主要特性
   A. 电压等级：20V AC;
   B. 电流：5A;
   C. 工作温度：-40° c~85° c;
3. 电气要求：
   A. 接触电阻:40mΩ Max,(初始),50mΩ Max。(最后);
   B. 电压：100V AC 1分钟;
   C. 绝缘电阻：100MΩ min。DC 500v;
4. 机械性能：
   A. 插入力：5~20N。（从1~10,000次）;
   B. 拔出力：8~20N。（从1~1,000次）;
      6~20N.（从1,001~10,000次）;
   C. 耐久性寿命：10,000次;







SECTION A-A



PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	GND	B1	GND





X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: TYPE-C 16P 四脚插立贴5.6 脚长0.95带弹
.XX ±0.10	.XX° ± 0.5°		
.XXX ± 0.05		FINISH	APPD: / DWG NO.: TYPE-C-16P-H5.6-05838
		Q'TY	CHKD: / SCALE 1/1 / SHEET 1/1 / REV. A1
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD