



RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		











NOTES:

1.MATERIAL:
- MOLDING: LCP UL94 V-0
- CONTACT:COPPER ALLOY.
- GOLD PLATED Min ON CONTACT AREA,100u''
- Min TIN (LEAD FREE) ON SOLDER AREA,
- SHELL: SUS201-H,T=0.25±0.03mm
- 50u'' NICKEL PLATING OVER ALL.

2.MECHANICAL:
- INSERTION: 5~20N.
- EXTRACTION: 8~20N AFTER TEST.
- DURABILITY: 5000 CYCLES

3.ELECTRICAL:
- CURRENT: 3A FOR VBUS;
- 1.25A FOR GND PIN.
- 0.25A FOR OTHER.
- VOLTAGE: 20 V MAX
- WITHSTANDING VOLTAGE: 100V AC R.M.S.
- CONTACT RESISTANCE: 40mΩ MAX.
- INSULATION RESISTANCE: 100MΩ MIN.

4.ENVIRONMENTAL
- TEMPERATURE RANGE -25°C ~ +85°C

5. 尺寸标注事项：
图示有标示"XX"者为首样全检，重点管控尺寸.

6. 产品符合RoHS标准.

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.10	.XX° ± 0.5°	MAT'L
.XXX ±0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE: TYPE-C 6PF 立贴 H10.5

APPD:

CHKD:

DR:

DWG NO.: TYPE-C-6P-H10.5-13026

SCALE	SHEET	REV.
1/1	1/1	A1