
REV.	ECN NUMBER	DESCRIPTION	DAET	DRAWN	CHECKED	APPROVED
A	/	NEW	2023.01.04	QIANG	GONG	LEO



NOTES:

1. MATERIAL:
   - HOUSING: HIGHT-TEMP PLASTIC,UL 94V-0,COLOR:NATURE;
   - COVER: HIGHT-TEMP PLASTIC,UL 94V-0,COLOR:BLACK;
   - TERMINAL: COPPER ALLOY;
   - PEG: ALLOY;
2. PLATING:
   - TERMINAL: GOLD PLATED ON NICKEL OVERALL.
   - PEG: TIN PLATED ON NICKEL OVERALL.
3. RATING:
   - CURRENT RATING: 0.3A AC/DC
   - VOLTAGE RATING: 30V AC/DC
   - TEMPERATURE RANGE: -55°C~+85°C;

CPT 元精技术

GENERAL	TOLERANCE	UNITS: mm	SCALE 1 : 1
X. ± 0.30	X.° ± 5°	APRROVED	LEO
.X ± 0.20	.X° ± 3°	CHECKED	GONG
.XX ± 0.15	.XX° ± 2°	DESIGNED	Qiang

TITLE:	0.3P 1.0H FPC W/COVER BACK-LOCK SMT TYPE
DRAWING NO. :	C-FC0005R-02 A
PART NO. :	FC0005R**B 1/3

REV.	ECN NUMBER	DESCRIPTION	DAET	DRAWN	CHECKED	APPROVED
A	/	NEW	2023.01.04	QIANG	GONG	LEO

PIN NO.(N)	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	NOTES
09	4.90	1.80	2.40	3.03	4.35	3.00	
11	5.50	2.40	3.00	3.63	4.95	3.60	
13	6.10	3.00	3.60	4.23	5.55	4.20	
15	6.70	3.60	4.20	4.83	6.15	4.80	
17	7.30	4.20	4.80	5.43	6.75	5.40	
19	7.90	4.80	5.40	6.03	7.35	6.00	
21	8.50	5.40	6.00	6.63	7.95	6.60	
23	9.10	6.00	6.60	7.23	8.55	7.20	
25	9.70	6.60	7.20	7.83	9.15	7.80	
27	10.30	7.20	7.80	8.43	9.75	8.40	
29	10.90	7.80	8.40	9.03	10.35	9.00	
31	11.50	8.40	9.00	9.63	10.95	9.60	
33	12.10	9.00	9.60	10.23	11.55	10.20	
35	12.70	9.60	10.20	10.83	12.15	10.80	
37	13.30	10.20	10.80	11.43	12.75	11.40	
39	13.90	10.80	11.40	12.03	13.35	12.00	
41	14.50	11.40	12.00	12.63	13.95	12.60	
43	15.10	12.00	12.60	13.23	14.55	13.20	
45	15.70	12.60	13.20	13.83	15.15	13.80	
47	16.30	13.20	13.80	14.43	15.75	14.40	
49	16.90	13.80	14.40	15.03	16.35	15.00	
51	17.50	14.40	15.00	15.63	16.95	15.60	
53	18.10	15.00	15.60	16.23	17.55	16.20	
55	18.70	15.60	16.20	16.83	18.15	16.80	Long Cover type
57	19.30	16.20	16.80	17.43	18.75	17.40	
59	19.90	16.80	17.40	18.03	19.35	18.00	
61	20.50	17.40	18.00	18.63	19.95	18.60	
63	21.10	18.00	18.60	19.23	20.55	19.20	
65	21.70	18.60	19.20	19.83	21.15	19.80	
67	22.30	19.20	19.80	20.43	21.75	20.40	
69	22.90	19.80	20.40	21.03	22.35	21.00	
71	23.50	20.40	21.00	21.63	22.95	21.60	

料号说明:


FC0005R ** B

- B: A=0.3Pitch A款; B=0.3Pitch B款
- **: Pin数码; 09=9Pin; 71=71Pin


GENERAL	TOLERANCE	UNITS: mm	SCALE 1 : 1	TITLE:	0.3P 1.0H FPC W/COVER BACK-LOCK SMT TYPE
X. ± 0.30	X.° ± 5°	APRROVED	LEO	DRAWING NO. :	C-FC0005R-02 A
.X ± 0.20	.X° ± 3°	CHECKED	GONG	PART NO. :	FC0005R**B 2/3
.XX ± 0.15	.XX° ± 2°	DESIGNED	Qiang		

元精技术


REV.	ECN NUMBER	DESCRIPTION	DAET	DRAWN	CHECKED	APPROVED
A	/	NEW	2023.01.04	QIANG	GONG	LEO



DIRECTION OF UNREELING



TRAILER TAPING(FREE) LEADER



STYLE AND DIMENSION OF REEL

PER REEL 4000 PCS

PACKING DISCRIPTION:

PIN No.	09~39	41~51	53~71
REEL WIDTH	24.4	32.4	44.4
PCS/REEL	5000	5000	5000
REEL/BOX	9	7	6
BOX/PCS	45K	35K	30K
CTN. SIZE	400*400*300		

PIN NO.	DIM W	DIM F	DIM So
13~39	24.0	11.50±0.10	--
41~51	32.0	14.20±0.10	28.4
53~71	44.0	20.20±0.15	40.4

元精技术

GENERAL	TOLERANCE	UNITS: mm	SCALE 1 : 1
X. ± 0.30	X.° ± 5°	APRROVED	LEO
.X ± 0.20	.X° ± 3°	CHECKED	Gong
.XX ± 0.15	.XX° ± 2°	DESIGNED	Qiang

TITLE: 0.3P 1.0H FPC W/COVER BACK-LOCK SMT TYPE

DRAWING NO. : C-FC0005R-02 A

PART NO. : FC0005R**B 3/3