




* All Raw Material, Manufacturing, Plating process comply with ROHS












RECOMMENDED PCB LAYOURT
TOLERANCE: ±0.05



Technical Speciality
技术特性
Rated Voltage:50V AC/DC Max
额定电压:50V AC/DC Max
Current Rating:1.0A Max
额定电流:1.0A Max
Insulation Resistance:1000MΩ Min
绝缘电阻:1000MΩ Min
Contact Resistance:100mΩ Max
接触电阻:100mΩ Max
Withstand Voltage:
耐压:500V AC/minute
Operating Temperature:-40℃ ~+85℃
工作温度:-40℃ ~+85℃

REMARKS:
附注:
1. MATERIAL:
材料:
1.1 HOUSING: LCP THERMOPLASTIC
本体:LCP 热塑性塑胶料
COLOR:WHITE.
颜色:白色/黑色
1.2 COVER: LCP THERMOPLASTIC
盖子:LCP 热塑性塑胶料
COLOR:WHITE
颜色:白色 /黑色
1.2 CONTACT: COPPER ALLOY
接触件:磷铜
2.PLATING:
表面处理:
2.1 CONTACT:
NICKEL AND 50u" MIN.COTACT Au",PAD TIN 80u" /MIN
接触件:镀镍底50u",接触点金Au",焊脚锡80u"。

SIM卡引脚功能定义

触电号	分 配	触电号	分 配
C1	电源电压 VCC	C5	地 GND
C2	复位 RST	C6	编程电压 VPP
C3	时钟 CLK	C7	输入/输出 I/O
C4	不提供触点	C8	不提供触点

REVISION NO.	ECR NO.	DESCRIPTION	MARK	DATE


广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD


DIMENSIONS INIT: mm
UNLESS OTHERWISE SPECIFIABLE


DIMENSION	TOLERANCE
X.X: ±	0.15
X.XX: ±	0.10
X.XXX: ±	0.05
ANGULAR: ±	1°


PRODUCT NAME : SIM掀盖式 6pin带柱子	DRAWING:	DATE: 2017/11/10	
PRODUCT NO. : SMB5FS1063T1	CHECK:	DATE: 2017/11/10	
DRAWING NO. :	APPROVED:	DATE: 2017/11/10	
	SCALE: 1:1	DWG ID: C D	REV.: A / PAGE: 1 OF 1

版本	变更内容	日　期	变更人
A	新图制成	--	--









技术要求：

1. 圆孔十个孔距离累计允许公差为±0.20mm.
2. 带长250mm内容许弯曲度1mm.
3. A_0/B_0尺寸由槽底0.30mm高处定义之.
4. K_0尺寸由槽底内表面处至成型上表面处定义之.
5. 所有尺寸定义依循EIA-481-C系准则定义之.
6. 材料：透明PET材质.
7. 材料厚度：0.30±0.05MM.
8. 13″单卷可装长度：19.8 Meter(206模）.
9. 13″单卷可装颗料：700+20psc（前后共空20格）.
10. 未注明拔模斜度为5°.
11. 重点检验尺寸代号：W、P_0、P、P_2、E、F、T、A_0、B_0、K_0.
12. 上盖带：自粘37.5*200M/R

一盘 :1.24KG
一箱 :7.44KG+纸箱 0.4KG=一箱总重7.84KG
一箱 :4200pcs/Carton
*纸箱规格 :350*350*330*

W	44.00 +0.30 −0.30	P	24.00 +0.10 −0.10	A_0	18.15 +0.15 −0.15	B_0	30.89 +0.15 −0.15
S	40.40 +0.10 −0.10	P_0	4.00 +0.10 −0.10	A_1	+0.15 −0.15	B_1	+0.15 −0.15
E	1.75 +0.10 −0.10	P_2	2.00 +0.15 −0.15	A_2	+0.10 −0.10	B_2	+0.10 −0.10
F	20.20 +0.15 −0.15	D_0	Ø1.50 +0.10 −0.00	K_0	3.25 +0.10 −0.10		
T	0.30 +0.05 −0.05	D_1	+0.10 −0.10	K_1	2.95 +0.10 −0.10		

广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD

料号:	SMB5FS1063T1		
日期:	--	料号:	
制图:	--	模号:	
核准:	--	客户版本	A
比例:	1:1	单位: mm	版本: A