



NO.	ECN NO.	DESCRIPTION	DATE





A–A





RECOMMENDED PCB LAYOUT

Note:

1: Material(材料）:
- Housing: PA46+30%GF （胶芯：PA46）
- Barrel: Brass C3604 （针管：黄铜 C3604）
- Plunger: Brass C3604 （针头：黄铜 C3604）
- Spring: SUS304 （弹簧：SUS304）
- Magnet: NdFeB （磁铁：钕铁硼）

2: Plating(电镀）:
- Barrel: 3u' Au over 50~80u' Ni(针管：镀金3u'，镍底50~80u'。）
- Plunger: 3u' Au over 50~80'u Ni（针头：镀金3u'，镍底50~80u'。）
- Spring: No plated (弹簧：不电镀）
- Magnet ：Ni plated（磁铁：镀镍）

3: Electrical(电气特性）:
- Rated Current & Voltage: DC 12V;1A （额定电压&电流：直流12V,1A）
- Contact Resistance: 50 mohm Max. at working height.
- 接触电阻：最大50毫欧（在工作高度状态下）
- Insulation Resistance: 1,000MΩ minimum. （绝缘电阻：1,000MΩ以上）
- Dielectric Withstand Voltage: 500VAC/minute. （抗击电压：500VAC/minute）

4: Mechanical(机械性能）:
- Force: 20g±5g at working height. (20g±5g 在工作高度）。
- Durability: 10.000 cycles(min)（寿命：10000次）

5: WorkTemperture(工作环境):
- Withstanding Higt Temperature: 280℃
- Operational Temperature: －40℃~ ＋85℃

深圳市鑫探技术有限公司
HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2026.9.17	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZCR00215030-05025-01
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			