



REV.	REVISION DESCRIPTION	DATE	APPD










NOTES:


1. Rated voltage: 50V AC.DC
2. Rated current: 1A AC DC
3. Contact resistance: ≤30 mΩ
4. lnsulation resistance: ≥100 MΩ
5. Withstand voltage: 500V AC/minute
6. Ambient temprature:-40℃～+105℃
7. Material :Nylon UL94V-0 750℃
8. Color：Black


Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2X2	SHLD-4Y-750-BK	1.0	6.7	2.7	2X12	SHLD-24Y-750-BK	11.0	16.7	12.7
2X3	SHLD-6Y-750-BK	2.0	7.7	3.7	2X13	SHLD-26Y-750-BK	12.0	17.7	13.7
2X4	SHLD-8Y-750-BK	3.0	8.7	4.7	2X14	SHLD-28Y-750-BK	13.0	18.7	14.7
2X5	SHLD-10Y-750-BK	4.0	9.7	5.7	2X15	SHLD-30Y-750-BK	14.0	19.7	15.7
2X6	SHLD-12Y-750-BK	5.0	10.7	6.7	～	～	～	～	～
2X7	SHLD-14Y-750-BK	6.0	11.7	7.7	2X20	SHLD-40Y-750-BK	19.0	24.7	20.7
2X8	SHLD-16Y-750-BK	7.0	12.7	8.7	～	～	～	～	～
2X9	SHLD-18Y-750-BK	8.0	13.7	9.7	2X25	SHLD-50Y-750-BK	24.0	29.7	25.7
2X10	SHLD-20Y-750-BK	9.0	14.7	10.7	～	～	～	～	～
2X11	SHLD-22Y-750-BK	10.0	15.7	11.7	2X30	SHLD-60Y-750-BK	29.0	34.7	30.7


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO .,LTD		
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SHLD-Y-750-BK		TITLE: 1.0mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:21/05/02	PART NO:
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21/05/02	SCALE: N/A / PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:21/05/02	UNITS: mm / REV.: A
DRAWING NO:				

REV.	REVISION DESCRIPTION	DATE	APPD










NOTES:


1. Rated voltage: 50V AC.DC
2. Rated current: 1A AC DC
3. Contact resistance: ≤30 mΩ
4. Insulation resistance: ≥100 MΩ
5. Withstand voltage: 500V AC/minute
6. Ambient temprature:-40℃～+105℃
7. Material :Nylon UL94V-0 750℃

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2X2	SHLD-4Y-750	1.0	6.7	2.7	2X12	SHLD-24Y-750	11.0	16.7	12.7
2X3	SHLD-6Y-750	2.0	7.7	3.7	2X13	SHLD-26Y-750	12.0	17.7	13.7
2X4	SHLD-8Y-750	3.0	8.7	4.7	2X14	SHLD-28Y-750	13.0	18.7	14.7
2X5	SHLD-10Y-750	4.0	9.7	5.7	2X15	SHLD-30Y-750	14.0	19.7	15.7
2X6	SHLD-12Y-750	5.0	10.7	6.7	～	～	～	～	～
2X7	SHLD-14Y-750	6.0	11.7	7.7	2X20	SHLD-40Y-750	19.0	24.7	20.7
2X8	SHLD-16Y-750	7.0	12.7	8.7	～	～	～	～	～
2X9	SHLD-18Y-750	8.0	13.7	9.7	2X25	SHLD-50Y-750	24.0	29.7	25.7
2X10	SHLD-20Y-750	9.0	14.7	10.7	～	～	～	～	～
2X11	SHLD-22Y-750	10.0	15.7	11.7	2X30	SHLD-60Y-750	29.0	34.7	30.7


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO .,LTD		
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SHLD-Y-750		TITLE: 1.0mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:21/05/02	PART NO:
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21/05/02	SCALE: N/A / PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:21/05/02	UNITS: mm / REV.: A
DRAWING NO:				

REV.	REVISION DESCRIPTION	DATE	APPD






SECTION A-A



SECTION B-B



SECTION C-C

NOTES:


1. Rated voltage: 50V AC.DC
2. Rated current: 1A AC DC
3. Contact resistance: ≤30 mΩ
4. Insulation resistance: ≥100 MΩ
5. Withstand voltage: 500V AC/minute
6. Ambient temprature:-40℃～+105℃
7. Wire range: AWG#32～#28


Materials:


8. Terminal: Phosphor bronze,Tin plated


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD		
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SHLD-T		TITLE: 1.0 mm Pitch Crimp Terminal
.XX: ± 0.2	.X° : ± 2.0°	DR: Chen Quan Long	DATE:21/10/22	PART NO:
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21/10/22	SCALE: N/A / PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:21/10/22	UNITS: mm / REV.: A0
DRAWING NO:				

REV.	REVISION DESCRIPTION	DATE	APPD










NOTES:

1. Rated voltage: 50V AC.DC
2. Rated current: 1A AC DC
3. Contact resistance: ≤30 mΩ
4. Insulation resistance: ≥100 MΩ
5. Withstand voltage: 500V AC/minute
6. Ambient temprature:-40℃～+105℃
7. Material :LCP UL94V-0
8. Material :Phosphor bronze/Tin plated

序号	图号	名称	材料	数量	附件
3	3	基座	LCP	1	UL94-V0
2	2	焊片	磷青铜	2	镀锡
1	1	接触件	磷青铜	N*	镀锡



PCB LAYOUT

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2X2	SHLD-4AB	1.0	5.0	2.9	2X12	SHLD-24AB	11.0	15.0	12.9
2X3	SHLD-6AB	2.0	6.0	3.9	2X13	SHLD-26AB	12.0	16.0	13.9
2X4	SHLD-8AB	3.0	7.0	4.9	2X14	SHLD-28AB	13.0	17.0	14.9
2X5	SHLD-10AB	4.0	8.0	5.9	2X15	SHLD-30AB	14.0	18.0	15.9
2X6	SHLD-12AB	5.0	9.0	6.9	2X16	SHLD-32AB	15.0	19.0	16.9
2X7	SHLD-14AB	6.0	10.0	7.9	2X17	SHLD-34AB	16.0	20.0	17.9
2X8	SHLD-16AB	7.0	11.0	8.9	2X18	SHLD-36AB	17.0	21.0	18.9
2X9	SHLD-18AB	8.0	12.0	9.9	2X19	SHLD-38AB	18.0	22.0	19.9
2X10	SHLD-20AB	9.0	13.0	10.9	～	～	～	～	～
2X11	SHLD-22AB	10.0	14.0	11.9	2X30	SHLD-60AB	29.0	33.0	30.9

GENERAL TOLERANCES (UNLESS SPECIFIED)

.X: ± 0.25	X° : ± 3.0°
.XX: ± 0.15	.X° : ± 2.0°
.XXX: ± 0.01	.XX° : ± 1.0°

FINISH:

DRAWING NO:

ZHEJIANG DELI CONNECTORS CO .,LTD

PRODUCT NAME: SHLD-AB

TITLE: 1.0mm Pitch Wire To Board SMT Wafer


PART NO:


DR:Chen Quan Long	DATE:18/05/02
CHKD: Wu Hui	DATE:18/05/02
APPD:Ren An De	DATE:18/05/02


SCALE: N/A PAGE: 1/1


UNITS: mm REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD
			Wu










NOTES:

1. Rated voltage: 50V AC.DC
2. Rated current: 1A AC DC
3. Contact resistance: ≤30 mΩ
4. lnsulation resistance: ≥100 MΩ
5. Withstand voltage: 500V AC/minute
6. Ambient temprature:-40℃～+105℃
7. Material :LCP UL94V-0
8. Material :Phosphor bronze/Tin plated

序号	图号	名称	材料	数量	附件
3	③	基座	LCP	1	UL94-V0
2	②	焊片	磷青铜	2	镀锡
1	①	接触件	磷青铜	N*	镀锡



Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2X2	SHLD-4AWB	1.0	5.0	2.9	2X12	SHLD-24AWB	11.0	15.0	12.9
2X3	SHLD-6AWB	2.0	6.0	3.9	2X13	SHLD-26AWB	12.0	16.0	13.9
2X4	SHLD-8AWB	3.0	7.0	4.9	2X14	SHLD-28AWB	13.0	17.0	14.9
2X5	SHLD-10AWB	4.0	8.0	5.9	2X15	SHLD-30AWB	14.0	18.0	15.9
2X6	SHLD-12AWB	5.0	9.0	6.9	2X16	SHLD-32AWB	15.0	19.0	16.9
2X7	SHLD-14AWB	6.0	10.0	7.9	2X17	SHLD-34AWB	16.0	20.0	17.9
2X8	SHLD-16AWB	7.0	11.0	8.9	2X18	SHLD-36AWB	17.0	21.0	18.9
2X9	SHLD-18AWB	8.0	12.0	9.9	2X19	SHLD-38AWB	18.0	22.0	19.9
2X10	SHLD-20AWB	9.0	13.0	10.9	～	～	～	～	～
2X11	SHLD-22AWB	10.0	14.0	11.9	2X30	SHLD-60AWB	29.0	33.0	30.9

GENERAL TOLERANCES (UNLESS SPECIFIED)

.X: ± 0.25	X° : ± 3.0°
.XX: ± 0.15	.X° : ± 2.0°
.XXX: ± 0.01	.XX° : ± 1.0°
FINISH:	
DRAWING NO:	

ZHEJIANG DELI CONNECTORS CO .,LTD

PRODUCT NAME: SHLD-AWB		TITLE: 1.0mm Pitch Wire To Board SMT Wafer
DR:Chen Quan Long	DATE:18/05/02	PART NO:
CHKD: Wu Hui	DATE:18/05/02	SCALE: N/A / PAGE: 1/1
APPD:Ren An De	DATE:18/05/02	UNITS: mm / REV.: B