


| REV | DESCRIPTION | DRAWIN/DATE | CHECK/DATE | APPROVED/DATE |
|---|---|---|---|---|
| A0 | NEW RELEASE | | | |
| A1 | 加宽弹片、加大开关PIN孔 | | | |
| A2 | 降低弹片预压值，防止变形 | | | |
| A3 | 接地端子直接MOLDING | | | |




PCB LAYOUT TOLERANCE+0.05/-0.05mm

| PIN NO. | CONNECTOR TERMINAL |
|---|---|
| P0 | SWITCH |
| P1 | VCC: PWR SIGNAL AND GND |
| P2 | RST: RESET SIGNAL |
| P3 | CLK: CLOCKING SIGNAL |
| P4 | GND: RWR SIGNAL AND GND |
| P5 | VPP: PROGRAMMING VOLTAGE |
| P6 | I/O: SERIAL DATA INPUT/OUTPUT |

NOTE:
1.ELECTRICAL PERFORMANCE:
CONTACT RESISTANCE:100mΩ Max
DIELECTRIC STRENGTH:500V AC FOR 1 MINUTE.
2.MECHANICAL PERFORMANCE:
INSERTION FORCE:0.5kgf~1.5kgf
EJECTION FORCE:0.5kgf~1.5kgf
CYCLE LIFE:5000 TIMES.

**C 1 0 1 1-0-3 3 1 0**


- 2-SUS201
- 3-SUS304
- 3-镀镍
- 1-刷金G/F
- 黑色
- 1-G/F
- 2-3U″
- 3-5U″
- 4-10U″
- 5-15U″


| GENERAL TOLERANCE | | ANGLE TOLERANCE | |
|---|---|---|---|
| X. | ±0.38 | X.° | ±2.0° |
| .X | ±0.25 | .X° | ±1.0° |
| .XX | ±0.13 | .XX° | ±0.5° |
| .XXX | ±0.05 | | |

广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD


| | | | | | | | |
|---|---|---|---|---|---|---|---|
| MAJOR(QC CHECKED) | SCALE 1 : 1 | DESIGN | | DATE | | TITLE | 6+1 PIN PUSH SIM CARD CONNETORCUT TYPE) | |
| ▼ = 7 places | UNIT mm | CHECKED | | DATE | | SERIES | SIM CARD SERIES | SIZE A4 |
| SHEET 1 OF 1 | | APPROVED | | DATE | | DRAWIN NO. | C1011-C-00 | REV. A2 |

| REV | DESCRIPTION | DRAWIN/DATE | CHECK/DATE | APPROVED/DATE |
|---|---|---|---|---|
| 0 | NEW RELEASE | CJL 2013/07/16 | | |





600 pcs/ Reel




600 pcs/ Reel * 6 = 3600 pcs




3600 pcs./Outer Carton

标签

AOWEN

厂 商:
订 单 号:
料 号:
品 名:
数 量:
出料日期:

| 项次 | 品名 | 料号 | 规格 | 用量(pcs) |
|---|---|---|---|---|
| 8 | 三角板 | C2001-7-2004 | 102*102*140*290mm | 4PCS |
| 7 | PE袋 | C2001-5-5001 | 开口570*长570*厚0.07mm | 1PCS |
| 6 | 干燥剂 | C2001-5-5002 | | 1PCS |
| 5 | 纸箱 | C2001-7-2001 | A=A L345*W345*H305 | 1 |
| 4 | 圆盘 | C1001-7-3003 | REEL13" | 1 |
| 3 | 上带 | C1001-7-3002 | W37.5 | 17.5m |
| 2 | 载料带 | C1001-7-3001 | P28*W44 | 17.5m |
| 1 | 6+1PIN SIM | C1011-0-23X0 | 6+1PIN SIM卡座镀金G/F,外壳不锈钢镀镍 | 3600 |

注意事项:

1. 每盘包装600PCS，不能少装，漏装；
2. 包装时前留6个空格，后留14个空格；
3. 每箱包装6盘，共计3600PCS，最上面一盘贴QC PASS标签；
4. 厂商，订单号，品名，料号，数量，日期必须书写正确；
5. 出厂标签粘贴在规定纸箱左上角。

| GENERAL TOLERANCE | ANGLE TOLERANCE |
|---|---|
| X. ±0.38 | X.° ±2.0° |
| .X ±0.25 | .X° ±1.0° |
| .XX ±0.13 | .XX° ±0.5° |
| .XXX ±0.05 | |

广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD

| | | | | | | | |
|---|---|---|---|---|---|---|---|
| MAJOR(QC CHECKED) | SCALE 1 : 1 | DESIGN | | DATE | | TITLE | SIM CARD PACK DRAWING |
| ▼ = x places | UNIT mm | CHECKED | | DATE | | SERIES | SIM CARD SERIES / SIZE A4 |
| SHEET 1 OF 1 | | APPROVED | | DATE | | DRAWIN NO. | C1011-P-01 / REV. 0 |