




MATING HEIGHT




GT-C5001 H F -1 02 X 01

- **G-Switch**
- **Series No**
- **Connector** H-Housing
- **F-Female**
- **Row NO** 1-Single Row
- **Pin Q' PY** 02
- **Housing Colour** W-White







G-Switch Specification:

1.Current rated: 13.0A AC/DC 14 AWG Teflon Electric Wire,
Waterproof grade:IP68(Anti immersion type)
10.5A AC/DC 16 AWG Silicone Rubber Electric Wire,
Waterproof grade:IP69K
2.Voltage rating: 300V AC/DC
3.Withstanding voltage:3000V AC
4.Contact resistance: 10mΩ max.
5.Insulation resistance: 1000MΩ min
6.Durability cycle: 50Cycles
7.Removal force: 5.0kgf/Pin min
8.Operating temperature range: -40°C ~ +85°C

IP69K

IP68
1. 5m/30min

Pb Process Capable
RoHS Compliant
EU RoHS Standards

NO.	PART NAME	MATERIAL	REMARK
1	HOUSING	PBT,94V-0	WHITE

SCALE: 1:1	UNIT: mm	Title:	Housing 5.00mm Pitch WPJV Single Row Female
SIZE: A4			
Unless otherwise General Tolerance:		Molde Code:	GT-C5001HF-102X01
X ±0.40			
X.x ±0.30			
X.xx ±0.20			
X° ±5°			
X.x° ±3°			

DRAWN	CHECKED	APPROVED	DATE
Hu	Chen	Chen	2021.10.21

品赞科技 b-Switch ®
www.dg-switch.com

REV: A0 SHEET: 1/1