

Straight Type

PART NO:XDHF-AS0254-2*_N_P



Right Angle Type

PART NO:XDHF-AS0259-2*_N_P



Dimension

Position	2*5P	2*7P	2*8P	2*10P	2*12P
A±0.20	17.90	22.98	25.52	30.60	35.68
B±0.15	10.16	15.24	17.78	22.86	27.94

Position	2*13P	2*15P	2*17P	2*20P	2*25P
A±0.20	38.22	43.30	48.38	56.00	68.70
B±0.15	30.48	35.56	40.64	48.26	60.96

材质 Material:

绝缘体 Insulator: Glass filled PBT UL94V-0 ,Black
接触件 Contacts: Brass
电镀层 Plating: Whole Gold plated over Nickel

电气性能 Electrical Characteristics:

接触电阻 Contact Resistance: 30mΩmax. at DC 100mA
绝缘电阻 Insulator Resistance: 1000MΩmin. at 500V DC
耐压 Withstanding Voltage: 1000V AC/rms 50Hz For 1 minute
工作电流 Current Rating:3 AMP
使用温度范围 Operating Temperature: -55℃～+105℃

				TITLE	P.C.B SOCKET 2.54 凸位排母	GENERAL TOLERANCE x. ± ±0.3 x.x ±0.2 x.xx ±0.1	DRAWN BY / DATE
				SERIES			CHECKED BY / DATE
				CUSTOMER P/N		ANGLE TOLERANCE x. ± ±2° x.x ±1° x.xx ±0.5°	APPROVED BY / DATE
				UNITS	mm	PROJECTION	DRAWING NO. / SHEET 1 OF 1
SCALE	DESCRIPTION	CHK	DATE	SCALE	2:1		SHEET SIZE A4 / REV. A0

深圳市连欣科技有限公司