


HSF RoHS


SPECIFICATIONS
PERFORMANCE
Current Rating: 0.5A
Voltage Rating: 50V
Insulation Resistance:500MΩ Min
Contact Resistance:30mΩ Max
Voltage Withstand: 200V AC For 1Minute
Return Loss: < 10dB up to 5GHz
Insertion Loss: < 1.5dB up to 5GHz
ratng Temperature:−40℃ to +125℃


Material
Cap:Stainless steel
Contact:Phosphor Bronze
Contact Area Finish:Gold or Gold flash
Insulator Material:Polyester(UL94V−0)
Housing:LCP
Soldering temperature:260℃±5° 5S












Ordering Information

3710 F XXX 038 XX F R XX

No.of Pins 040=40P 060=60P 080=80P 100=100P 120=120P 140=140P	Plastics Height H=3.7	Contact Plating G3=2u" Gold G4=3u" Gold G5=5u" Gold G6=10u" Gold G7=15u" Gold G8=30u" Gold S0=Gold Flash/Matte-Tin S1=3u" Gold/Matte-Tin S2=5u" Gold/Matte-Tin S3=10u" Gold/Matte-Tin S4=15u" Gold/Matte-Tin S5=30u" Gold/Matte-Tin	Insulator Material Option F=LCP	Packing R=Reel+Cap	Stream Code 01~99	



No.of Contacts	Dimensions					
	A	B	C	D	E	F
24	8.80	15.36	13.70	11.24	12.38	13.80
40	15.20	21.76	20.10	17.64	18.78	20.20
50	19.20	25.76	24.10	21.64	22.78	24.20
60	23.20	29.76	28.10	25.64	26.78	28.20
80	31.20	37.76	36.10	33.64	34.78	36.20
100	39.20	45.76	44.10	41.64	42.78	44.20
120	47.20	53.76	52.10	49.64	50.78	52.20
140	55.20	61.76	60.10	57.64	58.78	60.20

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
	料号编码	3710FXX038XXFRXX	
A	2020.03.04	NEW DRAWING	

OPERATION		模号	AUJJ
X.X	±0.30		
X.XX	±0.20	CHECK	
X.XXX	±0.10		
Angle	±3°	APPROVE	
DIM	TOL		

SCALE	FIT
UNIT	mm
SIZE	A4
SHEET	1/1
PROJ.	

浙江创都电子科技有限公司

PART NO.	CAX-0.8BTB-M-40P-H3.7-TJ5.58-AUJJ
TITLE:	0.8BTB−NPIN H=3.7mm Female