HSF RoHS

SPECIFICATIONS

FEATURES:

Round cable angled exit 180°

Strain Relief Staple With Spring latches

Back Shell Desing by Die-Cast

Excellent EMI/RFI protection

MATERIALS:


Back Shell: Zinc Alloy, plated nickel over copper


Screw: Steel, nickel plated over copper


Cable Clipper: Steel, nickel plated


Contact Area: Copper Alloy, Gold Plated over Nickel

Insulator: PBT UL94V-0














剖面 A-A











	料号编码	6330-M068SSXXMNAXX		OPERATION		DRAW		16.08.03	SCALE	FIT
				X.X	±0.30				UNIT	mm
				X.XX	±0.20	CHECK	QHJL		SIZE	A4
A	2016.08.03	NEW DRAWING		X.XXX	±0.10				SHEET	1/1
				Angle	±3°	APPROVE			PROJ.	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL					

浙江创都电子科技有限公司

PART NO.	CAX-SCSI-DB68P-LGWK-6330-M068SS
TITLE:	HALF PITCH RIBBON CONNECTOR SCSI 68P DB-Type Male 180° 出线 锌合金外壳螺杆式