

5P~16P



2P~4P









P.C.B LAYOUT
TOLERANCE:±0.05

Ordering Information:

A2512WV-XP - *** - **
1 2 3

1.Part NO.
2.Material:
(Blank): Nylon 66,UL94V-0(White)
46: Nylon 46,UL94V-0(Beige)
GWT: Nylon 66,UL94V-0(Beige),IEC 60335-1,5th Edition Glow Wire Capable.
3.Finish:
(Blank): Tin over Nickel
G: Gold over Nickel

SPECIFICATIONS:

Current Rating: 3A AC,DC
Voltage Rating: 500V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 500MΩ Min
Withstanding Voltage: 1000V AC/minute
Pin Material: Brass

Ordering Information & Dimensions

Part NO.	Dimensions(mm)	
	A	B
A2512WV-2P	2.50	7.50
A2512WV-3P	5.00	10.00
A2512WV-4P	7.50	12.50
A2512WV-5P	10.00	15.00
A2512WV-6P	12.50	17.50
A2512WV-7P	15.00	20.00
A2512WV-8P	17.50	22.50
A2512WV-9P	20.00	25.00
A2512WV-10P	22.50	27.50
A2512WV-11P	25.00	30.00
A2512WV-12P	27.50	32.50
A2512WV-13P	30.00	35.00
A2512WV-14P	32.50	37.50
A2512WV-15P	35.00	40.00
A2512WV-16P	37.50	42.50
A2512WV-17P	40.00	45.00

REV	DESCRIPTION	DATE
A6	CHANGE THE DRAWING	2023.09.12
A5	CHANGE THE DRAWING	2022.12.21
A4	CHANGE THE DRAWING	2021.12.20
A3	CHANGE THE DRAWING	2020.08.08
A2	ADD THE COLOR RED	2019.05.15
A1	UPDATE THE ORDERING INFORMATION	2018.11.20
A0	NEW RELEASE	2005.07.01

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	3:1	1 of 1

DRWN	CHK'D	APPR
Xiaoyan Luo	Diankui Wan	Jack Yin

General Tolerances: x.x±0.25, x.xx±0.20, x.xxx±0.15, ANGLES ±1°

THIRD ANGLE PROJECTION

TITLE: 2.50mm PITCH VERTICAL WAFER

DRAWING NO.: A2512WV-XP

REV: A6