


REV.	ECN NO.	MODIFIED MARK	APPROVED
A	———	FIRST RELEASE	









PCB LYAOUT
TOP VIEW

COLOR TABLE

CODE	A	B
COLOR	WHITE	RED



SCHEMATIC



仅供参考

NOTES:
ELECTRICAL:
1: RATED CURRENT: 1A Max.
2: RATED VOLTAGE: 12V DC.
3: CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING: 100 MILLIOHMS Max.
4: INSULATION RESISTANCE: 100 MEGAOHMS Min.
5: DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1: INSERTION FORCE: 3N−30N.
2: WITHDRAWAL FORCE: 3N−30N.
3: DURRABILITY: 500 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: −20°C TO 60°C.

NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK
⑥	TERMINAL	2	BRASS t=0.45	CuSn PLATED	RoHS 2.0
⑤	SOCKET	2	BRASS t=0.4	CuSn PLATED	
④	COVER−B	1	ABS	BLACK	
③	COVER−A	1	ABS	BLACK	
②	WASHER	2	ABS	SEE COLOR TABLE	
①	HOUSE	1	ABS	BLACK	

ANGLE	±5°
63 < L	±0.5
16 < L ≤ 63	±0.4
4 < L ≤ 16	±0.3
L ≤ 4	±0.2

模号：HP

浙江创都电子科技有限公司

MAT'L: See table	DESIGN:	PART NO：CAX-AV-210FB-WR-HP			
FINISH: See table	CHECKED:				REV.: A
Q'TY: /	APPROVED:	UNIT: mm	VIEW:	SCALE: 5:1	SHEET: 1/1	SIZE: A3