
由 Autodesk 教育版产品制作

＊ 所有原料材质,生产制程,电镀必须符合ROHS要求



SEC A-A
SCALE 1:1

SPECIFICATION:
1.MATING FORCE:44.1N MAX
2.UNMATING FORCE:7-25N
Autodesk 3.DURABILITY: 5000 CYCLES MIN
4.CURRENT:0.5A
由 5.VOLTAGE:40V MAX
X2
6.WITHSTANDING VOLTAGE:500V AC MIN.(UNMATED)
7.CONTACT RESISTANCE:30MN MAX.
8.INSULATION RESISTANCE:100MN MIN.(UNMATED)
UnRegistered
9.OPERATING TEMPERATURE RANGE:-20.C TO +85.C
10.ALL THE MATERIAL SHOULD COMPLY WITH THE ROHS

浙江创都电子科技有限公司

DIMENSIONS INIT: mm UNLESS OTHERWISE SPECIFIABLE DIMENSION TOLERANCE X.X: ± 0.25 X.XX: ± 0.10 X.XXX: ± 0.05 ANGULAR: ± 1°	PRODUCT NAME : MiNi-HDMI 19Pin SMT C TYPE	DRAWING:	DATE: 2008/12/10
	PART NO : CAX-MINI-HDMI19P-CJ4.5-AUZ	CHECK:	DATE: 2008/12/10
	模号 : Z	APPROVED:	DATE: 2008/12/10
		SCALE: 1:1 / DWG ID: P D / REV.: B / PAGE: 1 OF 1	

REVISION NO.	ECR NO.	DESCRIPTION	MARK	DATE

由 Autodesk 教育版产品制作