



RoHS








外壳















Specification:


1. Contact Resistance: 35 m Ohm Max.
2. Insulation Resistance: 200 M Ohm Min. At 500V DC.
3. Contact Current Rating: 1 Amp AC/DC
3. Voltage Rating: 40V AC.
4. Withstanding Voltage: 500V AC For 1 Minute.
5. Operating Temperature: −25°c to +85°c
6. Wire Accomodation: 24,26,28 & 30 AWG

Material and Finish:

1. Insulator Material: Glass Reinforced Polyester(PBT) UL94−V0,Black
2. Contact Material: Phosphor Bronze
3. Shroud Material: Spcc
4. Contact Area Plated: Sn Over Nickel 50u".
5. Solder Area Plated: Tin Plated(80u" min Lead Free)




(六角螺母*2)




(短号十字螺丝*2)


(中号十字螺丝*2)



(长号十字螺丝*2)



(上线夹)



(下线夹)

				OPERATION		DRAW	YiYuSheng	20.11.13	SCALE	FIT	浙江创都电子科技有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	CAX-SCSI-SM-20P6331M020SS
				X.XXX	±0.10				SHEET	1/1		
A	2020.11.13	NEW DRAWING		Angle	±3°	APPROVE			PROJ.		TITLE:	SCSI SM 20Pin Solder type Male
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL							