


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	/		图面升级整理图纸	2024.09.06	阿树
A2	ECN-20250909-002	(A2) X3	产品改模，尺寸修正	2025.09.09	桑甚






02P~03P (1 LOCK)
Shape Scale 1:2





04P~05P (1 LOCK)
Shape Scale 1:2




06P~15P (2 LOCK)
Shape Scale 1:2

■SPECIFICATIONS
- Voltage rating:100V AC/DC
- Current rating:2A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥500MΩ
- Contact resistance:≤20mΩ






02P~06P



07P~11P




12P~15P


PART NO.:

X1515 H-02-PT
① ② ③ ④

①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~15P
(A2) ④Material:PT-PBT(Natural) UL94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.50	7.30	4.30	09	12.00	17.80	14.80
03	3.00	8.80	5.80	10	13.50	19.30	16.30
04	4.50	10.30	7.30	11	15.00	20.80	17.80
05	6.00	11.80	8.80	12	16.50	22.30	19.30
06	7.50	13.30	10.30	13	18.00	23.80	20.80
07	9.00	14.80	11.80	14	19.50	25.30	22.30
08	10.50	16.30	13.30	15	21.00	26.80	23.80





3D VIEW

X1515H-02-PT	PBT	X1515W	X1515T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB 星创 Connection

DESIGN	桑甚	VIEW:	MODEL TYPE: 1.50mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X1515H-02-PT
APPROVED		SIZE: A4	DWG NO.: X-X1515H-02-PT

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2