LUTETECH 陆特科技

LTC0603-0250FS FAST ACTING FUSE

Surface Mount Fuse

Electrical Characteristics/电气特性


% of Rated Current	Opening Time at 25℃
100%	4 hours, Minimum
200%	5 seconds, Maximum
300%	0.2 seconds, Maximum

Performance Specifications/电性参数

Part Number	Marking	Rated Current（A）	Rated Voltage V (Max.)	Interrupting Rating	Nominal Cold Resistance Ohms*	Nominal Melting I^2t A2sec **	Voltage Drop @ I rated mV typ.
LTC0603-0250FS	D	0.25	32	50A/32Vdc	1.3	0.0016	419.0

* Measured at 10% of rated current, 25°C. ** Measured at 0.001sec.

Product Dimensions (mm)/产品尺寸



Dimension	Min mm (inch)	Max mm (inch)
A	1.50 (0.059)	1.70 (0.067)
B	0.70 (0.027)	0.90 (0.035)
C	0.20 (0.008)	0.40 (0.016)
D	0.20 (0.008)	0.40 (0.016)

Packing/包装

Packaging Option	Quantity
LTC0603-0250FS	5000 pcs/reel

www.lutefuse.com
Tel:86-755-28704432 Email:sales@sl-fuse.cn
Specifications are subject to change without notice
Revision 2020