
HSF RoHS

NOTES:
1. Rating voltage:500V AC RMS
2. Rating current:1.0 A
3. Rating temperature:−55℃~105℃

4. Materials:
   - 4.1 Insulator:DBT UL94V−0
   - 4.2 Contact:Copper Alloy
   - 4.3 Back Shell:Zinc Alloy Nickel Plated
   - 4.4 Flat Screws:Steel Nickel Plated
   - 4.5 Cable Clipper:Steel Nickel Plated
   - 4.6 Jackscrews:Steel Nickel Plated



Y Type

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A	2020.09.28	NEW DRAWING	

OPERATION		DRAW		20.09.28
X.X	±0.30			
X.XX	±0.20	CHECK		
X.XXX	±0.10			
Angle	±3°	APPROVE		
DIM	TOL			

SCALE	FIT
UNIT	mm
SIZE	A4
SHEET	1/1
PROJ.	

浙江创都电子科技有限公司

PART NO.	CAX-DB100P-LGWK6330-M100S
料 号	