



RoHS











外壳



















(六角螺母*2)




(短号十字螺丝*2)


(中号十字螺丝*2)



(长号十字螺丝*2)



(上线夹)



(下线夹)

Specification:

1. Contact Resistance: 35 m Ohm Max.
2. Insulation Resistance: 200 M Ohm Min. At 500V DC.
3. Contact Current Rating: 1 Amp AC/DC
3. Voltage Rating: 40V AC.
4. Withstanding Voltage: 500V AC For 1 Minute.
5. Operating Temperature: −25°c to +85°c
6. Wire Accomodation: 24,26,28 & 30 AWG

Material and Finish:

1. Insulator Material: Glass Reinforced Polyester(PBT) UL94−V0,Black
2. Contact Material: Phosphor Bronze(C5191−EH)T=0.30
3. Shroud Material: Spcc
4. Contact Area Plated: Sn Over Nickel 50u".
5. Solder Area Plated: Tin Plated(80u" min Lead Free)

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A	2018.11.13	NEW DRAWING	

OPERATION		DRAW		18.11.13
X.X	±0.30			
X.XX	±0.20	CHECK		
X.XXX	±0.10			
Angle	±3°	APPROVE		
DIM	TOL			

SCALE	FIT
UNIT	mm
SIZE	A4
SHEET	1/1
PROJ.	

浙江创都电子科技有限公司

PART NO.	CAX-SCSI-SM-36P6331M036SS
TITLE:	SCSI SM 36Pin Solder type Male