HSF RoHS

SPECIFICATIONS

FEATURES:

Round cable angled exit 180°

Strain Relief Staple With Spring latches

Back Shell Desing by Die-Cast

Excellent EMI/RFI protection


MATERIALS:


Back Shell:Zinc plated nickel over copper


Spring latches:phosphor bronze over nickel


Screw:steel nickel plated over copper

Cable Clipper:steel nickel plated













剖面 A-A









	料号编码	6330-M068SSXXMNAXX		OPERATION		DRAW		16.08.03	SCALE	FIT
				X.X	±0.30				UNIT	mm
				X.XX	±0.20	CHECK			SIZE	A4
A	2016.08.03	NEW DRAWING		X.XXX	±0.10				SHEET	1/1
				Angle	±3°	APPROVE				
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL				PROJ.	

浙江创都电子科技有限公司

PART NO.	CAX-SCSI-CN68P-6330-M068SS
TITLE:	HALF PITCH RIBBON CONNECTOR SCSI 68P CN-Type Male 180° 出线 锌合金外壳 螺杆式