



REV	DESCRIPTION	DESIGN	DATE
A0			







PCB LAYOUT(Tolerance:±0.05)











Specifications:


Contact resistance:≤10mΩ
Insulation resistance:≥1000MΩ
Rated voltage:250V AC DC
Rated current:5.0A AC DC
Withstand Voltage: 1000V AC/minute
Temperature Range:−25℃～ +85℃
Housing:LCP UL94V−0,BLACK
Contacts:Brass/MATTE Sn−plated
Solder Tabs:Brass/MATTE Sn−plated
CAP:Stainless steel





PIN	DIM A	DIM B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
*9	24.00	30.65
*10	27.00	33.65
*11	30.00	36.65
*12	33.00	39.65

ORDER INFORMATION:



浙江创都电子科技有限公司

料号编码：A3001AWV-*-F9KB3-R-X

GENERAL	TOLERANCE		
X.	±0.50	X.	±5°
X.X	±0.30	X.X	±2°
X.XX	±0.20	X.XX	±1°
		UNITS:	mm

USE: CUSTOMER
APPD:
CHKD:
DR:

PART NO.: CAX-MX3.0-1D05A-LAT-GK

模号GK

SCALE 1 : 1

SHEET 1 / 1