



3P~20P



2P

Ordering Information:

A2512H-XP - **


1 2

1.Part NO.

2.Color:

(blank):White

RD:Red



SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 500V AC,DC


Temperature Range: -40°C ~ +105°C


Contact Resistance: 20mΩ Max

Insulation Resistance: 500MΩ Min

Withstanding Voltage: 1000V AC/minute

Material: Nylon66, UL94V-0 (White)





Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	2.50	6.80	12P	27.50	31.80
3P	5.00	9.30	13P	30.00	34.30
4P	7.50	11.80	14P	32.50	36.80
5P	10.00	14.30	15P	35.00	39.30
6P	12.50	16.80	16P	37.50	41.80
7P	15.00	19.30	17P	40.00	44.30
8P	17.50	21.80	18P	42.50	46.80
9P	20.00	24.30	19P	45.00	49.30
10P	22.50	26.80	20P	47.50	51.80
11P	25.00	29.30			

A3	JL-GC-ECN00903	2025.10.23
A2	DELETE THE SIZE C	2020.08.19
A1	CHANGE THE DRAWING	2019.04.16
A0	NEW RELEASE	2005.07.01
REV	DESCRIPTION	DATE

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	4:1	1 of 1

DRWN	CHK'D	APPR
Dengchun Yi	Diankui Wan	Jack Yin

General Tolerances

x.x±0.25
x.xx±0.20
x.xxx±0.15
ANGLES ±1°

THIRD ANGLE PROJECTION

TITLE

2.50mm PITCH HOUSING

DRAWING NO.

A2512H-XP

REV A3