
Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		9/26



NOTES:

1. ELECTRICAL:
   - 1.1. VOLTAGE RATING:DCV 300V 10MS
   - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
   - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
   - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
   - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
   - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	OD:2.5* 15 mm 套管	2
③	接头	MMCX 公头公针，弯头，镀金	1
②	接头	SMA防水母头母针，牙长11mm，直头，镀金	1
①	同轴线	RG178 CABLE，透明棕色FEP外被,OD:1.80mm	AS

CUSTOMER P/N:

深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM	DRAWN James	DATE 2026-08-27	KH-FSSMAK-MMCXJW-RG178-600MM
	CHKD. Frank	2026-08-27	TITLE: RG-178 CABLE SMA F TO MMCX M, L=600MM
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING	APPD. Scott	2026-08-27	
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1° ±0.3 ±0.25 ±0.150		SIZE B / DWG Number. / REV A
			SCALE:Free / TYPE / SHEET 1 OF 1