



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.06.17	
A2	N/A			2025.10.20	





Specification:
1.Rating:3A 250VAC
2.Contact resistance:≤30 mΩ
3.Insulation resistance:≥100 MΩ(DC500V/Min)
4.Electronics life: 10000 cycles
5.Operation force:250±100gf





SS−12M12 X X

Knob Type
L
G

H(mm)
2~12

Function		
ON	NA	ON
● ○	/	○ ●

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB Connection 星坤

DESIGN		VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS−12M12XX
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2