


RoHS Compliant


Pb Process Capable


REV.	ZONE	DESCRIPTION	DESIGN	DATE
C		UPGRADE DRAWING	ZXM	2025.05.09
D		载带高度变更	ZXM	2025.07.29





















RECOMMENDED PCB LAYOUT(t=0.80±0.05)
COMPONENT SIDE(GENERAL TOLERANCE:±0.05)



SECTION: A-A
SCALE 1:1







Added suction cap view
SCALE 1:1

NOTES:

SPECIFICATION:

1. CURRENT RATING: 3.0A MAX.
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 ° C ~ 85 ° C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX.
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NO.	DESCRIPTION	MATERIAL	REMARKS	Q'TY
6	HOUSING	HIGH TEMPERATURE PLASTIC, PA9T	BLACK	1PCS
5	CAP	HIGH TEMPERATURE PLASTIC, LCP	BLACK	1PCS
4	EMI	STAINLESS STEEL, SUS304	---	2PCS
3	LATCH	STAINLESS STEEL, SUS301	TIN: 80-120u"Min./Ni base: 50u"Min. Plated	1PCS
2	SHELL	STAINLESS STEEL, SUS304	Ni: 50u"Min. Plated	1PCS
1	INSERT MOLDING	HIGH TEMPERATURE PLASTIC (HOUSING, LCP; TERMINAL1, C5191)	CONTACT: Au: 1u"Min. Ni base 50u"Min., TIN: 50-120u", BLACK	2PCS

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.10		

UNITS: mm
MAT'L:
FINISH:
Q'TY:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE: TYPE-C 24PIN立式贴片公头 三支脚 H=11.1MM


APPD: CZN
CHKD: CZJ
DR: ZXM

PART NO.: TYPE-CM-24P-H11.1SMT-00143


SCALE	SHEET	REV.
1/1	1/2	D


RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	⚠	UPGRADE DRAWING	ZXM	2025.05.09
D	⚠	载带高度变更	ZXM	2025.07.29




① 产品入载带示意图







② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	300	3300

包装说明：

1. 将检验好的成品;SMT朝下放入载带底部;每卷装300PCS产品;具体如图一所示
2. 将包装好的产品;每盘必须贴上内标签;具体如图二所示
3. 将贴好内标签的产品每11盘叠;具体如图三所示
4. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   （产品包装的标签，如客户有要求，请按客户要求包装出货）
5. 载带前面留6PCS空格，后面留6PCS空格

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.20	.XX° ± 0.5°	MAT'L
.XXX ±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE: TYPE-C 24PIN立式贴片公头 三支脚 H=11.1MM

APPD: CZN

CHKD: CZJ

DR: ZXM

PART NO.: TYPE-CM-24P-H11.1SMT-00143

SCALE	SHEET	REV.
1/1	2/2	D