

RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW	ZXM	





NOTES：

特性：Specifications

电器 Electrical:

接触阻抗：初始最大不超过40mΩMax,测试后变化值不超过10mΩMax

耐电压：AC200V 60S/MIN,0.5mA Max:DC500V,60S/MIN,100ΩMax

绝缘阻抗：100M ohms MIN.

材料：Matorial:

主体：LCP料黑色耐高温塑胶

护套：LCP料黑色耐高温塑胶

端子：C5191磷铜 T=0.15MM.

外壳：不锈钢304 T=0.15MM。

卡勾：不锈钢301 T=0.30MM。

电镀规格：


端子：半金锡，接触点镀金1u，焊脚处镀锡40-80u.


外壳：镀镍


卡钩：前镍后锡

环保要求：ROHS,REACH标准.

包装方式：依客户需求（建议使用REEL包装）








RECOMMENDED P.C.B. LAYOUT

TOLERANCE UNSPECIFIED ±0.05mm



PIN ASSIGNMENTS:

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND			VBUS		D-	D+	CC		TX1-	TX1+	GND

B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
GND									RX1-	RX1+	GND

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	± 0.10		

UNITS mm

MAT'L

FINISH

Q'TY

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司

Guangdong Chuangyue Technology Co.,Ltd

TITLE: TYPE C 9PIN常规卡勾带插脚(铆压壳)

APPD: CZN

CHKD: CZJ

DR: ZXM

PART NO.: TYPE-CM-9P-H12.2-00119

SCALE	SHEET	REV.
1/1	1/1	B