


RoHS Compliant


Process Capable


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	---	NEW	ZXM	2025.03.14
















Added suction cap view
SCALE 1:1












RECOMMENDED PCB LAYOUT(t=0.80±0.05)
COMPONENT SIDE(GENERAL TOLERANCE:±0.05)



SECTION: A-A
SCALE 1:1

NOTES:

SPECIFICATION:

1. CURRENT RATING: 3.0A MAX.
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 ° C ~ 85 ° C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX.
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NO.	DESCRIPTION	MATERIAL	REMARKS	Q'TY
6	HOUSING	HIGH TEMPERATURE PLASTIC	PA9T, BLACK	1PCS
5	COVER	HIGH TEMPERATURE PLASTIC	LCP BLACK	1PCS
4	SPRING	STAINLESS STEEL	---	2PCS
3	LATCH	STAINLESS STEEL	TIN: 50-120u"/Ni base: 50u"Min. Plated	1PCS
2	SHELL	STAINLESS STEEL	Ni: 50u"Min. Plated	1PCS
1	TERMINALI HOUSING	HIGH TEMPERATURE PLASTIC	LCP BLACK/CONTACT: Au: 1u"Min. Ni base50u"Min. TIN: 50-120u"	2PCS

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	± 0.10		

UNITS: mm

MAT'L:

FINISH:

Q'TY:


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.


TITLE:
TYPE-C 24PIN立式贴片公头 四支脚 H=11.1MM宽脚（无弹片）


APPD:	CZN	PART NO.: TYPE-CM-24P-H11.1SMT-00139			
CHKD:	CZJ		SCALE	SHEET	REV.
DR:	ZXM		1/1	1/2	A

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	---	NEW	ZXM	2025.03.14




① 产品入载带示意图







② 卷盘贴标签示意图




③ 11盘产品叠层示意图





④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：

1. 将检验好的成品;SMT朝下放入载带底部;每卷装300PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每11盘叠;具体如图三所示
4. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
5. 载带前面留9PCS空格，后面留9PCS空格
6. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

	REEL	CARTON
CONNECTOR (PCS)	300	3300

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.20	.XX° ± 0.5°	MAT'L
.XXX ± 0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE: TYPE-C 24PIN立式贴片公头 四支脚 H=11.1MM宽脚（无弹片）

APPD: CZN

CHKD: CZJ

DR: ZXM

PART NO.: TYPE-CM-24P-H11.1SMT-00139

SCALE	SHEET	REV.
1/1	2/2	A