


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW	ZXM	










RECOMMEND PCB LAYOUT(THICKNESS=1.6mm)
TOLERANCE: ±0.05









Notes:

Specifications:

1. Current rating: 1 A Max.
2. Dielectric withstanding:voltage: 100V(AC) for 1 min.
3. Contact resistance: 50m Ω Max.
4. Insulation resistance: 100M Ω Min.
5. Total mating force: 3.57 Kgf Max.
6. Total unmating force: 1.0 Kgf Min.0.81~2.05 Kgf Min.after 10000 insertion/extration cycles
7. Temperature range: -30°C~+80°C
8. Material:

JGlue core: LCP black
Iron case: SUS201 T=0.3
Terminal: phosphorus copper T=0.15

MICRO USB B TYPE PIN ASSIGNMENTS

PIN NUMBER	1	2	3	4	5
SIGNAL NAME	VBUS	D−	D+	ID	GND


PART NO.:
10600 10
Plating Contacts:
08: Au 1u"
10: Au 3u"


X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: MICRO USB 5PIN立贴母座 三脚 高度H=6.7MM 卷边
.XX ±0.10	.XX° ± 0.5°	FINISH	APPD: / DWG NO.: MICRO-5P-H7.7SMT-00109
.XXX ± 0.05		Q'TY	CHKD: / DR: / SCALE 1/1 / SHEET 1/2 / REV. B


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

RoHS Compliant











① 产品入载带示意图

② 卷盘贴标签示意图

③ 7盘产品叠层示意图





⑤ 外箱封箱示意图

④ 产品入外箱示意图

	REEL	CARTON
CONNECTOR (PCS)	500	3500

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装500PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每7盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
6. 载带前面留10PCS空格，后面留10PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: MICRO USB 5PIN母座H6.2-7.7MM包装规范
.XX ±0.10	.XX° ± 0.5°	FINISH	APPD: / DWG NO.: MICRO-5P-H7.7SMT-00109
.XXX ±0.05		Q'TY	CHKD: / SCALE N/A / SHEET 2/2 / REV. B
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD