

RoHS Compliant


IPX7 1m/30min


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		





plug插入深度参考图








RECOMMENDED P.C.B. LAYOUT (T:1.00mm)

TOLERANCE UNSPECIFIED ±0.05mm

Note:
1.Material:
1.1 Housing: LCP
1.2 Contact:C7025,t=0.20mm
1.3 Shell: SUS316
2.ELECTRICAL:
2-1:CURUENT RATAING:
VBUS AND GND CONTACTS RATED AT 1.25A
PARALLELED FOR A TOTAL OF 5A;
2-2:INITIAL CONTACT RESISTANCE :40 MEGOHMS
2-3:DIEELECTRIC WITHSTANDING VOLTAGE:
100V AC MIN;
3:MECHANICAL CHARACTERISTICS:
3-1:MATING FORCE:5~20N
3-2:UNMATING FORCE:8~20N(INITIAL),
6~20N(AFTER 10000 CYCLES)
3-3:FREQUENCE: 200±50 CYCLES /HOUR,
10000 CYCLES
3-4:OPERATING TEMPERATURE ;-40°~80°.









USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
~~A2~~	~~TXp1~~	~~B11~~	~~RXp1~~
~~A3~~	~~TXn1~~	~~B10~~	~~RXn1~~
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
~~A10~~	~~RXn2~~	~~B3~~	~~TXn2~~
~~A11~~	~~RXp2~~	~~B2~~	~~TXp2~~
A12	GND	B1	GND





PART NUMBER LIST:

SERIDL NUMBER	PART NO	CONTACTS PLATING SPECIFICATION
①	1030012/CY-001-CF0050	contact area Aulu" weld zone Alu"
②	CY-001-CF0157	contact area Au3u" weld zone Alu"

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

UNITS mm

MAT'L

FINISH

Q'TY

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE:
TYPE-C 16PIN直立式防水母座单筋位6.68 外壳粉末冶金

APPD:

CHKD:


DR:

PART NO.:
TYPE-C-16P-H6.68SMT-00150


SCALE	SHEET	REV.
1/1	1/1	A

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		




① 产品入载带示意图




② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装500PCS产品;
2. 将包装好的产品;每盘必须贴上内标签;
3. 将贴好内标签的产品每11盘叠;
4. 装好后并封好纸箱及贴好相关标签;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
5. 载带前面留14PCS空格，后面留14PCS空格

	REEL	CARTON
CONNECTOR (PCS)	500	5500

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.20	.XX° ± 0.5°	MAT'L
.XXX ±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE:
TYPE-C 16PIN直立式防水母座单筋位6.68 外壳粉末冶金

APPD:

CHKD:

DR:

PART NO.:
TYPE-C-16P-H6.68SMT-00150

SCALE	SHEET	REV.
1/1	1/1	A