



RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		

















SECTION:A-A

特性：

一、电气性能：E1CTRICAL

1. 额定电流： 3.0A
2. 接触阻抗：40 MILLIOHMS MAX
3. 耐电压：150V AC / 1 mA MAX
4. 绝缘阻抗：150V DC/100 MEGA OHMS MIN

二、机械性能：

1. 插入力：5~20N
2. 拔出力：8~20N
3. 使用寿命：10000次、拔出力 5N MIN

三、材料：MATERIAL

1. 塑胶：LCP UL94V-0
2. 端子：C2680 T=0.15MM
3. 外壳：SUS304 T=0.30MM
4. 卡勾：SUS301 T=0.15MM

四、电镀:FINISH

1. 端子：接触点镀金1U"MIN
   PIN脚焊接区域镀金1U"MIN.
2. 外壳：镀镍80U"MIN（盐雾48H）

五、电镀品需做粘锡测试：粘锡面积达到95%以上。

六、SMT回流焊（峰值260°C±5°C）不能起泡、熔胶、变色不良（变形在公差范围以内）

七、工作温度：-55°C~+85°C

八、盐雾测试：通过48H在浓度为5±1%盐水的盐雾测试无生锈现象

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.20	.XX° ± 0.5°	MAT'L
.XXX ±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE: TYPE C 16PIN沉板1.6MM母座 长L=7.35MM

APPD: CZN

CHKD: CZJ


DR: ZXM

DWG NO.: TYPE-C-16P-R1.6L7.35-00188


SCALE	SHEET	REV.
1/1	1/2	A

RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		



AFTER MATING



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.80MM;DEFAULT TOLERANCE:±0.05

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME
A1	GND
A4	VBUS
A5	CC1
A6	D+
A7	D−
A8	SBU1
A9	VBUS
A12	GND

PIN NUMBER	SIGNAL NAME
B12	GND
B9	VBUS
B8	SBU2
B7	D−
B6	D+
B5	CC2
B4	VBUS
B1	GND

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.20	.XX° ± 0.5°	MAT'L
.XXX ± 0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE: TYPE-C 16PIN沉板1.6MM母座 长L=7.35MM

APPD: CZN

CHKD: CZJ


DR: ZXM

DWG NO.: TYPE-C-16P-R1.6L7.35-00188


SCALE	SHEET	REV.
1/1	2/2	A

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		




① 产品入载带示意图




② 卷盘贴标签示意图



③ 10盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装1000PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每10盘叠;具体如图三图四所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   （产品包装的标签，如客户有要求，请按客户要求包装出货）
6. 载带前面留10PCS空格，后面留10PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	MAT'L
.XX ±0.20	.XX° ± 0.5°	
.XXX ± 0.10		FINISH
		Q'TY

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司

TITLE: TYPE-C 16PIN沉板1.6MM母座 长L=7.35MM

APPD: CZN
CHKD: CZJ
DR: ZXM

DWG NO.: TYPE-C-16P-R1.6L7.35-00188

SCALE	SHEET	REV.
1/1	1/1	A