


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B	---	DRAWING UPGRADE	ZXM	2024.08.31
C	---	DRAWING UPGRADE		












USB TYPE C 接线示意图	
A4、A9、B9、B4	V
A5	
B5	
A1、A12、B1、B12	G
A6	D+
A7	D-
(R1=56KΩ R3=56KΩ) 5%	





RECOMMENDED PCB LAYOUT(t=0.80±0.05)
COMPONENT SIDE(GENERAL TOLERANCE:±0.05)

NOTES:
1.MECHANICAL:
MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.
2.ELECTRICAL:
CURRENT: 3.0A MAX
VOLTAGE: 5V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 40 mΩ MAX INITIAL;
50 mΩ MAX AFTER 10000 CYCLES
3.ENVIRONMENTAL
OPERATING TEMPERATURE RANGE -40°C ~ +85°C

表1

品名	规格
1030024	LCP黑
1030025	LCP白
1030026	PA9T黑
1030027	PA9T白


NO.	DESCRIPTION	QTY.	MATERIAL	TREATMENT
4	GND LATCH	1	STAINLESS STEEL	NI 30u" Min. PLATED OVERALL, TAB WITH LEAD FREE TIN 50u"Min.
3	CONTACT	16	COPPER ALLOY	NI 30u" Min. UNDER PLATING OVER ALL,G/F PLATING AT - CONTACT AREA.LEAD FREE TIN 50u"Min. AT TERMINATION.
2	SHELL	1	STAINLESS STEEL	Ni 30u" Min. UNDER PLATED OVER ALL.
1	HOUSING	2	THERMOPLASTIC UL 94V-0	MOLDED COLOR:BLACK/WHITE

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.20	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN立式贴片公头 高H=11.94MM
.XXX ±0.10			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD: PART NO TYPE-CM-16P-H11.94SMT-00104
		Q'TY	CHKD:
			DR:


SCALE	SHEET	REV.
1/1	1/2	C


RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B	---	DRAWING UPGRADE	ZXM	2024.08.31
C	---	DRAWING UPGRADE		




① 产品入载带示意图







② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装400PCS产品;具体如图一所示
2. 将包装好的产品;每盘必须贴上内标签;具体如图二所示
3. 将贴好内标签的产品每11盘叠;具体如图三所示
4. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
5. 载带前面留8PCS空格，后面留8PCS空格
6. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

	REEL	CARTON
CONNECTOR (PCS)	400	4400

X. ±0.50	X.° ± 2°	UNITS	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	mm	
.XX ±0.20	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN立式贴片公头 高H=11.94MM
.XXX ±0.10		FINISH	APPD: / PART NO: TYPE-CM-16P-H11.94SMT-00104
		Q'TY	CHKD: / DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

SCALE	SHEET	REV.
1/1	1/2	C