


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		




独立视图









NOTES:

1. MATERIAL AND FINISH SEE TABLE
2. ELECTRICAL REQUIREMENTS:
   - 2-1. CURRENT RATING: 2A PER PIN.
   - 2-2. CONTACT RESISTANCE: 30mOhm MAX.
   - 2-3. INSULATION RESISTANCE: 1000MOhm MIN. 500VDC FOR 1 MINUTE.
   - 2-4. WITHSTANDING STRENGTH: 500V AC FOR 1 MINUTE.
3. MECHANICAL REQUIREMENTS:
   - 3-1. DURABILITY: 10,000 CYCLES.
4. ENVIRONMENT REQUIREMENTS:
   - 4-1. OPERATING TEMP.: -30°C TO +85°C
   - 4-2. STORAGE TEMPERATURE: -40°C TO +85°C
5. PLEASE CONTACT PROMAX SALES REPRESENTATIVE TO VERIFY PRODUCT DETAILS.

PART NAME	MATERIAL	DESCRIPTION
SHELL	SUS304	PLATED Ni
HOUSING	PBT	COLOR: BLACK;
TERMINAL	C5191	UNDER PLATED: SEE PART NO.; CONTACT AREA FINISH SEE PART NO. SOLDER AREA: 80u" Min TIN PLATED;

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.10	.XX° ± 0.5°	MAT'L
.XXX ±0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE: 4PIN斜度USB

APPD:

CHKD:

DR:

DWG NO.: USB2.0-AF-4P-00101

SCALE	SHEET	REV.
1/1	1/1	A