


由 Autodesk 教育版产品制作


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		


RoHS Compliant

















备注(NOTE):
1材质:
1.1胶芯：LCP UL94 V-0
1.2端子：C2680,T=0.2mm；镍底，镀金
1.3外壳：不锈钢SUS304 1/2 T=0.25*26.5 表面镀镍
2.电气特性:
2.1.接触区：接触电阻40mΩ Max,允许10mΩ变化量. 测试条件:20mv，100mA下测量.
2.2.接触电流：3A VBUS引脚；1.25A用于GND引脚；其他引脚为0.25A.
2.3.额定电压：5V.
2.4.耐电电压：100VAC.
2.5.绝缘电阻：至少100兆欧 .
3.机械性能:
3.1.插入力：0.5-2.0Kg
3.2.拔出力：0.6-2.04Kg
3.3.插拔次数：5000次.
4.工作环境：-20℃ to +85℃.

USB TYPE C PIN ASSIGNMENTS

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND			VBUS				CC1				
				CC1				VBUS			GND
B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 6PIN直插 H=6.8mm(不居中款外露2.00mm IPX6)
.XXX ± 0.05			
		FINISH	APPD: / DWG NO.: TYPE-C-6P-H6.8-00190
		Q'TY	CHKD: / SCALE 1/1 / SHEET 1/1 / REV. A1
			DR:

由 Autodesk 教育版产品制作