


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	---	NEW	---	---
B	---	DRAWING UPGRADE	LJW	2024.12.17







NOTES:
1. CURRENT RATING: 5A MAX.
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: −40 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX.
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES
9. Water Resistance: IPX7











RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



USB TYPE-C PIN ASSIGNMENTS:

PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

建议防水圈



1：材料：粉色硅胶，符合ROHS环境管理物质.
2：尺寸：外径: 3.37X9.20, 内径: 2.13X7.96,
胶边厚: 1.0, 胶边高: 1.0

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.15		

UNITS: mm
MAT'L:
FINISH:
Q'TY:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司

TITLE: TYPE−C 6PIN板上四脚插板防水母座 粉末冶金双圈 IPX7

APPD: CZN
CHKD: CZJ
DR: LJW

PART NO.: TYPE-C-6P-L7.1-00120

SCALE	SHEET	REV.
1/1	1/1	B