



RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		INITIAL DRAWINGS	ZXM	2024/05/19














备注：

1.材质：

1.1胶芯：LCP+30%G.F UL94V-0

1.2端子：黄铜，T=0.15mm；镍底，镀金1μ"

1.3外壳：不锈钢，T=0.30mm；表面镀镍100μ"
或亮锡100μ"

2.主要特性：

2.1额定电流：5.0A

2.2接触阻抗：30mΩ MAX

2.3绝缘阻抗：100MΩ MIN 250V DC

2.4耐压测试：250V AC

2.5沾锡性：温度250±5℃，时间5±0.5s

2.6整体插入力：5N~20N
整体拔出力:8N~20N


2.7使用寿命：10000次

2.8工作温度：−30℃～+80℃


X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN立贴母座 H=7.5
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD: / DWG NO.: TYPE-C-16P-H7.5SMT-001139
		Q'TY	CHKD: / SCALE 1/1 / SHEET 1/3 / REV. A
			DR:

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		INITIAL DRAWINGS	ZXM	2024/05/19



SECTION:A–A
SCALE 1:1



Added suction cover view



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

USB TYPE–C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.10	.XX° ± 0.5°	MAT'L
.XXX ± 0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司

TITLE: TYPE-C 16PIN立贴母座 H=7.5

APPD:

CHKD:


DR:

DWG NO.: TYPE-C-16P-H7.5SMT-001139


SCALE	SHEET	REV.
1/1	2/3	A


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		INITIAL DRAWINGS	ZXM	2024/05/19

RoHS Compliant





① 产品入载带示意图






② 卷盘贴标签示意图






③ 7盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	11	5500

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装500PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每11盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
6. 载带前面留18PCS空格，后面留18PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: TYPE-C 16PIN立贴母座 H=7.5 包规
.XX ±0.10	.XX° ± 0.5°		
.XXX ± 0.05		FINISH	APPD: / DWG NO.: TYPE-C-16P-H7.5SMT-001139
		Q'TY	CHKD: / SCALE 1/1 / SHEET 3/3 / REV. A
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD