



RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	---	NEW		
B	---	DRAWING UPGRADE	LJW	2025.07.10












Notes:


Specifications:


1. Current rating: 1 A Max.
2. Dielectric withstanding: voltage: 100V(AC) for 1 min.
3. Contact resistance: 50m Max.
4. Insulation resistance: 100M Min.
5. Total mating force: 3.57 Kgf Max.
6. Total unmating force: 1.0 Kgf Min.0.81~2.05 Kgf Min.after 10000insertion/extration cycle
7. Temperature range: −30°C~+80°C
8. Transmission rate : 480Mbps
9. Material/plating specifications
   - Terminal : C5191, T=0.15 electroplated half gold nickel 1u" gold
   - Case: 201 Stainless Steel T=0.30 continuous Nickel plating 30u"
   - Glue core : LCP black
10. Salt spray 24H



RECOMMEND PCB LAYOUT(THICKNESS=1.6mm)

TOLERANCE: ±0.05





MICRO USB B TYPE PIN ASSIGNMENTS

PIN NUMBER	1	2	3	4	5
SIGNAL NAME	VBUS	D−	D+	ID	GND


X. ±0.50	X.° ± 2°	UNITS	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		Guangdong Chuangyue Technology Co.,Ltd
.XX ±0.20	.XX° ± 0.5°	MAT'L	TITLE: MICRO USB 5PIN立贴母座 三脚 高度H=10.5MM 卷边
.XXX ± 0.10		FINISH	APPD: CZN / DWG NO.: MICRO-5P-H10.5SMT-00103
		Q'TY	CHKD: CZJ
			DR: LJW

SCALE	SHEET	REV.
1/1	1/2	B


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Guangdong CHUANGYUE TECHNOLOGY CO., LTD

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	---	NEW		
B	---	DRAWING UPGRADE	LJW	2025.07.10




① 产品入载带示意图




② 卷盘贴标签示意图



③ 产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	400	4400

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装400PCS产品;
2. 将包装好的产品;每盘必须贴上内标签;
3. 将贴好内标签的产品每11盘叠;
4. 装好后并封好纸箱及贴好相关标签;
   （产品包装的标签，如客户有要求，请按客户要求包装出货）
5. 载带前面留12PCS空格，后面留12PCS空格

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司 Guangdong Chuangyue Technology Co.,Ltd
.X ±0.30	.X° ± 1°	MAT'L	TITLE: MICRO USB 5PIN立贴母座 三脚 高度H=10.5MM 卷边
.XX ±0.20	.XX° ± 0.5°	FINISH	APPD: CZN / DWG NO.: MICRO-5P-H10.5SMT-00103
.XXX ±0.10		Q'TY	CHKD: CZJ
			DR: LJW

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Guangdong CHUANGYUE TECHNOLOGY CO., LTD

SCALE	SHEET	REV.
1/1	2/2	B