


RoHS Compliant


| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|---|---|---|---|---|
| B | | NEW | | |











RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ±0.05








NOTES:
SPECIFICATION:
1. CURRENT RATING: 3.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30° C~+85° C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN
6. LNSERTION FORCE: 5N~20N
7. UNMATING FORCE: 8N-20N
8. DURABILITY: 10000 CYCLES
9. WATER PROOFNESS:THISPRODUCTIS BASED ON IPX7.

PIN ASSIGNMENT:

| PIN NO | A1&B12 | A4&B9 | A9&B4 | A12&B1 |
|---|---|---|---|---|
| SIGNAL NAME | GND | VBUS | VBUS | GND |
| PCB PAD NO. | | | | |




加防水圈示意图


TABLE:

| NO | PART | Q'TY | Material |
|---|---|---|---|
| 1 | SHELL | 1 | STAINLESS STEEL,NI PLATED |
| 2 | CONTACT | 6 | COPPER STEEL,TIN/Au/NI PLATED |
| 3 | MID PLATE | 1 | STAINLESS STEEL,NO PLATING |
| 4 | 1MD HOUSING | 1 | HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0 |
| 5 | 2MD HOUSING | 1 | HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0 |
| 6 | SHIELDING PLATE | 1 | STAINLESS STEEL,NI PLATED |


| | | | |
|---|---|---|---|
| X. ±0.50 | X.° ± 2° | UNITS mm | 广东创粤科技有限公司 |
| .X ±0.30 | .X° ± 1° | | |
| .XX ±0.10 | .XX° ± 0.5° | MAT'L | TITLE: TYPE-C 4PIN板上防水母座(外壳两脚插板,端子SMT) |
| .XXX ±0.05 | | | |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD | | FINISH | APPD: / DWG NO.: TYPE-C-4P-L7.9-00101 |
| | | Q'TY | CHKD: / SCALE 1/1 / SHEET 1/2 / REV. A1 |
| | | | DR: |

| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|---|---|---|---|---|
| B | | NEW | | |


RoHS Compliant





① 产品入载带示意图





② 卷盘贴标签示意图




③ 7盘产品叠层示意图




④ 产品入外箱示意图




⑤ 外箱封箱示意图

| | REEL | CARTON |
|---|---|---|
| CONNECTOR (PCS) | 700 | 4900 |

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装700PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每7盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
6. 载带前面留16PCS空格，后面留16PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165° -180°

| | | | |
|---|---|---|---|
| X. ±0.50 | X.° ± 2° | UNITS mm | 广东创粤科技有限公司 |
| .X ±0.30 | .X° ± 1° | MAT'L | TITLE: TYPE-C 4PIN/6PIN/16PIN板上防水母座包装规范 |
| .XX ±0.10 | .XX° ± 0.5° | | |
| .XXX ±0.05 | | FINISH | APPD: / DWG NO.: TYPE-C-4P-L7.9-00101 |
| | | Q'TY | CHKD: / SCALE 1/1 / SHEET 2/2 / REV. A1 |
| | | | DR: |

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD