

RoHS Compliant


Process Capable


30 Min/1m
IP-X7


REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	---	UPGRADER DRAWINGS	ZXM	2025.12.23














Note:

1.Material:

1.1 Housing: PA9T,BLACK
1.2 Contact: C7025,T=0.15mm
1.3 Shell: SUS304,T=0.3mm
1.4 Mid plate: SUS301,T=0.15mm
1.5 Ground plate: SUS304,T=0.2mm
1.6 Molding: LCP,BLACK,UL94V-0

2.ELECTRICAL:

2-1:CURUENT RATAING:
VBUS AND GND CONTACTS RATED AT 1.25A PARALLELED FOR A TOTAL OF 3A;
2-2:INITIAL CONTACT RESISTANCE :40 MEGOHMS
2-3:DIEELECTRIC WITHSTANDING VOLTAGE:
100V AC MIN;

3.PLATING SPECIFICATION:

3-1.CONTACTS:
Ni 50u" MIN.UNDER PLATED OVER ALL.
Au 1u" PLATED ON THE FUNCTIONAL AREA OF CONTACT.GOLD FLASH PLATED ON SOLDER AREA.
3-2.SHELL:
Ni 30u" MIN.UNDER PLATED OVER ALL.
3-3.MID PLATE:
CLEAR ONLY

4.MECHANICAL CHARACTERISTICS:

4-1:MATING FORCE: 5~20N
4-2:UNMATING FORCE: 8~20N(INITIAL), 6~20N(AFTER 10000 CYCLES),
4-3:FREQUENCE: 200±50 CYCLES /HOUR, 10000 CYCLES
4-4:OPERATING TEMPERATURE ;-40°~+85°.

5.IR REFLOW:

THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.

PIN ASSIGNMENT:

Pin No.	Signal Name	Pin No.	Signal Name
A1	GND	B12	GND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	GND	B1	GND

X. ±0.50	X.° ± 2°	UNITS	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	mm	Guangdong Chuangyue Technology Co.,Ltd.
.XX ±0.20	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN沉板4脚插板防水母座 头部外露1.2中心高1.28
.XXX ±0.10		FINISH	APPD: CZN / PART NO.: TYPE-C-16P-R1.0L6.8-00186
		Q'TY	CHKD: CZJ
			DR: ZXM

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

SCALE	SHEET	REV.
1/1	1/3	C


RoHS Compliant


Process Capable

30 Mln/1m
IP-X7

REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	---	UPGRADER DRAWINGS	ZXM	2025.12.23


密封开孔参考尺寸(只供参考),组装外壳时需要打环保润滑油






装配方向


组装示意图



plug插入深度参考图



RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ±0.05



胶圈使用尺寸参考图

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.10		

UNITS: mm

MAT'L:

FINISH:

Q'TY:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE: TYPE-C 16PIN沉板4脚插板防水母座
头部外露1.2中心高1.28

APPD: CZN

CHKD: CZJ

DR: ZXM

PART NO.: TYPE-C-16P-R1.0L6.8-00186


SCALE	SHEET	REV.
1/1	2/3	C

REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	---	UPGRADER DRAWINGS	ZXM	2025.12.23


RoHS Compliant

Process Capable


30 Min/1m
IP-X7




① 产品入载带示意图




② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：
1. 将检验好的成品；SMT朝下放入载带底部；每卷装700PCS产品；
2. 将包装好的产品；每盘必须贴上内标签；
3. 将贴好内标签的产品每11盘叠；
4. 装好后并封好纸箱及贴好相关标签；
（产品包装的标签，如客户有要求，请按客户要求包装出货）
5. 载带前面留16PCS空格，后面留16PCS空格

	REEL	CARTON
CONNECTOR (PCS)	700	7700

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.10		

UNITS: mm
MAT'L:
FINISH:
Q'TY:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE: TYPE-C 16PIN沉板4脚插板防水母座
头部外露1.2中心高1.28

APPD: CZN
CHKD: CZJ
DR: ZXM

PART NO.: TYPE-C-16P-R1.0L6.8-00186

SCALE	SHEET	REV.
1/1	3/3	C