


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		

RoHS Compliant


Process Capable







胶圈使用尺寸参考图




plug插入深度参考图

装配方向


组装示意图


开孔尺寸参考

组装外壳时需要打环保润滑油




Suggested adsorption size







Note:
1.Material:
1.1 Housing: LCP
1.2 Contact:C7025,t=0.20mm
1.3 Shell: SUS316
2.ELECTRICAL:
2-1:CURUENT RATAING:
VBUS AND GND CONTACTS RATED AT 1.25A PARALLELED FOR A TOTAL OF 5A;
2-2:INITIAL CONTACT RESISTANCE :40 MEGOHMS
2-3:DIEELECTRIC WITHSTANDING VOLTAGE: 100V AC MIN;
3:MECHANICAL CHARACTERISTICS:
3-1:MATING FORCE:5~20N
3-2:UNMATING FORCE:8~20N(INITIAL), 6~20N(AFTER 10000 CYCLES)
3-3:FREQUENCE: 200±50 CYCLES /HOUR, 10000 CYCLES
3-4:OPERATING TEMPERATURE ;-40°~80°.



Added suction cover view





RECOMMENDED P.C.B. LAYOUT (T:1.00mm)

TOLERANCE UNSPECIFIED ±0.05mm

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

UNITS mm

MAT'L

FINISH

Q'TY

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd

TITLE:
TYPE-C 24PIN直立式防水母座双筋位7.50 外壳粉末冶金

APPD:

CHKD:


DR:

PART NO.:
TYPE-C-24P-H7.50SMT-00155


SCALE	SHEET	REV.
1/1	1/2	A

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		


RoHS Compliant




① 产品入载带示意图




② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装500PCS产品;
2. 将包装好的产品;每盘必须贴上内标签;
3. 将贴好内标签的产品每11盘叠;
4. 装好后并封好纸箱及贴好相关标签;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
5. 载带前面留14PCS空格，后面留14PCS空格

	REEL	CARTON
CONNECTOR (PCS)	500	5500

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.20	.XX° ± 0.5°	MAT'L
.XXX ±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

FINISH

Q'TY

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd

TITLE:
TYPE-C 24PIN直立式防水母座双筋位7.50 外壳粉末冶金

APPD:

CHKD:

DR:

PART NO.:
TYPE-C-24P-H7.50SMT-00155

SCALE	SHEET	REV.
1/1	2/2	A