
RoHS

REV.	ECN.#	DESCRIPTION	NAME	DATE
A0	————	NEW RELEASE	liuhongping	2023.01.02
A1	————	换新图框	huhaoteng	2023.11.14



技术要求：


1. 产品外观无脏污，刮伤，变形现象
2. 塑体无毛边，未射饱；接触片无氧化，生锈现象

备注：1. 接触片镀金层的厚度可根据客户的需求做变更

2. 铜柱插稍处点胶

Current Rating : 0.5A AC/DC max.
Voltage Rating : 10V AC/DC
Contact Resistance: 100mΩ max.
Insulation Resistance: 1000MΩ min./500VDC
Normal Force: 0.5N/pin MIN.
Temperature: −40℃ to 85℃ .

序号	名称	材料	数量	备注
7	端子	磷铜	8	底层镀Ni；接触区镀Au15u″
6	Z形片	不锈钢	1	
5	小轴	磷铜	1	
4	推杆	不锈钢	1	
3	弹簧	不锈钢	1	
2	按钮	LCP黄色	1	
1	塑胶主体	LCP黑色	1	



RECOMMENDED PCB LAYOUT 未注公差±0.05

C1 ——→ VCC
C2 ——→ RST
C3 ——→ CLK
C5 ——→ GND
C6 ——→ VPP
C7 ——→ I/O
K1 (SW1)
K2 (SW2)


MILLIMETERS	INCH
X.° ±2°	X.° ±2°
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.?Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

东莞市金比莱五金塑胶科技有限公司
DongGuan JinBiLai Metal Plastic TechnologyCo,.Ltd


TITLE	3.0H PIN-PUSH SIM CARD(铜柱插销处点胶)				DR	
PART NO.	102154002-A				CHKD	
PRO J.	PAGE	1/2	UNITS	mm	APPD	
	SIZE	A4	SCALE	1:1	DIS NO.	

RoHS





NOTES


1. NUMBER OF CONNECTORS: 500PCS/REEL
2. LEAD TAPE LENGTH




3.QUANTITY: 2000PCS/CARTON









MILLIMETERS	INCH
X.° ±2°	X.° ±2°
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.?Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

东莞市金比莱五金塑胶科技有限公司
DongGuan JinBiLai Metal Plastic TechnologyCo,.Ltd

TITLE	3.0H PIN-PUSH SIM CARD(铜柱插销处点胶)				DR	
PART NO.	102154002-A				CHKD	
PRO J.	PAGE	2/2	UNITS	mm	APPD	
	SIZE	A4	SCALE	1:1	DIS NO.	