
MR-3

Aliases (USEZ3000000000)

KEMET, MR, Current, Round - Toroidal, Zero Phase Current, High Sensitivity, Compact



Click here for the 3D model.

General Information	
类别	MR
类型	Current
样式	Round - Toroidal
描述	Zero-Phase Current Transformers
特征	High Sensitivity, Compact
引线	Cables
RoHS	Yes
REACH	Yes
注释	Measurement Conditions: f=60Hz, R=300 Ohms, Io=22.5 mAmps

Dimensions	
D	11mm MIN
H	10.5mm MAX
D2	28mm MAX
D3	30.5mm MAX
D4	6mm NOM
LL	67mm +/-3mm

Specifications	
温度范围	-20/+80°C
直流电压	8 mV MIN (Output)
电流传感器	60 Amps
等效串联电阻 (ESR)	30 Ohms
其他	Overinput characteristics (After DC5A input) = 10% MAX.

Packaging Specifications	
包装	Tray
包装数量	300
典型元件重量	11.9 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO